

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053082212](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 12 Circuits, Natural, Glow-Wire Capable

Documents:

| | |
|--|---|
| Drawing (PDF) | Product Specification PS-105300-100-001 (PDF) |
| 3D Model | Application Specification AS-105300-100-001 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-105308-100-000 (PDF) |
| Product Specification 1053001000-PS-CH-000 (PDF) | Test Summary 1053000000-TS-000 (PDF) |
| Product Specification 1053001000-PS-ES-000 (PDF) | Test Summary 1053001000-TS-000 (PDF) |
| Product Specification 1053001000-PS-JP-000 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification 1053001000-PS-SK-000 (PDF) | Product Literature (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 105308 |
| Application | Power, Wire-to-Board |
| Comments | Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold |
| Overview | Nano-Fit Power Connectors |
| Product Name | Nano-Fit |
| UPC | 889056023894 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (maximum) | 12 |
| Color - Resin | Natural |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 1.050/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.50mm |
| Pitch - Termination Interface | 2.50mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C, -40° to +115°C |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 6.5A |
|-------------------------------|------|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|---|
| Application Specification | AS-105300-100-001 |
| Packaging Specification | PK-105308-100-000 |
| Product Specification | 1053001000-PS-CH-000, 1053001000-PS-ES-000, 1053001000-PS-JP-000, 1053001000-PS-SK-000, PS-105300-100-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105308](#) Series

Mates With

Nano-Fit Vertical Through Hole Headers
[1053102112](#) , [1053102212](#) , [1053102312](#) ,
[1053122112](#) , [1053122212](#) , [1053122312](#) .
 Nano-Fit Right-Angle Through Hole Headers
[1053142112](#) , [1053142212](#) , [1053142312](#) .
 Nano-Fit Vertical SMT Headers [1054292112](#)
 , [1054292212](#) , [1054292312](#) , [1054292412](#)
 . Nano-Fit Right-Angle SMT Headers
[1054052112](#) , [1054052212](#) , [1054052312](#)
 . Nano-Fit Plug Housings [2014442112](#) ,
[2014442212](#)

Use With

Nano-Fit Crimp Terminal [105300](#)
 Nano-Fit Pre-Crimped Leads (Gold)

[797582129](#) , [797582130](#)
 Nano-Fit Pre-Crimped Leads (Tin)

[797582139](#) , [797582140](#)
 Nano-Fit TPA Retainer
[105325](#)

This document was generated on 10/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION