

## SDUC offset steel boring bar, positive, right

for longitudinal and copy turning using DC indexable insert

**ATORN**<sup>®</sup>

### Application


For longitudinal and copy turning with DC 55° indexable insert.

### Version

- precision-manufactured **steel** boring bar, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

### Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



<b>Art. No.</b>	<b>17847 012</b>
<b>ISO name</b>	A 10 H SDUC R/L 07
<b>Min. bore diameter</b>	14 mm
<b>Shaft diameter</b>	10 mm
<b>Cutting edge height</b>	4.5 mm
<b>Clearance length</b>	8 mm
<b>Length</b>	100 mm
<b>Clamping surface height</b>	9 mm
<b>Programming size</b>	7 mm
<b>Suitable for indexable inserts</b>	DC.. 0702..
<b>Tool design</b>	Right
<b>DIN</b>	8024

### EAN-Code

4050293344158