




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Latching Block**

Features

Product Type Features

Product Type	Accessory
Latch Type	Latching Block With Threaded Hole
D-Shaped Connector Accessories	Latching Block

Body Features

Latch Material	Zinc
----------------	------

Mechanical Attachment

Screw Plating Material	Zinc
Screw Material	Steel
Screw Finish	None
Panel Attachment Style	Front Mount
Screw & Hole Thread Size	4-40 UNC 2B

Packaging Features

Packaging Quantity	2
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 745255-2
SPRING LATCH 2/BAG



TE Part # 208101-4
HDP LATCHING BLOCK

Also in the Series | AMPLIMITE HDP-20



D-Sub Locking & Mounting(9)



PCB D-Sub Connectors(13)


Customers Also Bought



TE Part #205206-8
D-Sub Crimp: Plug, Signal, 15 Posn,
Pin Size 20, Shell Size 2



TE Part #T4130412041-000
M12 Panel Mount Solder Cups



TE Part #1-5745172-3
AMPLI CBL CLMP KIT



TE Part #1-34142-1
PG R 22-16 COMM 22-18 MIL 6



TE Part #2-1625876-6
CBT 1/2 5% 2R2



TE Part #103321-3
03 MODII HDR SRST B/A .100CL



TE Part #1658641-2
D-Sub Crimp: Plug, Signal, 50 Posn,
Pin Size 20, Shell Size 5



TE Part #2-1437667-6
4DB-P108-04=4DB ASSEMBLY



TE Part #1218441-3
R/A PLG ASSY 25 POS SER 109



TE Part #1-640719-0
02P UMNL STR/REL & INSRT NATL

Documents

Product Drawings

LATCH BLOCK (SZ 1-4)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_208101-8_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_208101-8_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_208101-8_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English