ETD-BL-1T-ON-CC-...

Timer relay with switch-on delay (with control contact) and adjustable time

INTERFACE

Data sheet 103616_en_02

© PHOENIX CONTACT 2010-06-07



1 Description

Compact time relay in the 6.2 mm housing in order to control – time sequences. –

The time is set on the front side using a labeled knurled wheel — which is sunk in order to prevent unintentional adjustment. — The time can be set using a screwdriver (blade width _ _ 2.5 mm).

The compact time relays are available with varied time ranges as well as with screw and spring-cage connections.

Features

- 6.2 mm narrow housing
- With switch-on delay (with control contact)
- Adjustable time
- Easy and accurate time setting
- Supply voltage 24 V DC
- Output: A floating PDT



WARNING: Risk of electric shock

Never carry out work when voltage is present.



Make sure you always use the latest documentation. It can be downloaded at www.phoenixcontact.net/catalog.



This data sheet is valid for all products listed on the following page:



2 Ordering data


| Description | Туре | Order No. | Pcs. / Pkt. |
|---|---------------------------|-----------|-------------|
| Timer relay with screw connection | | | |
| Time range 0.110 s | ETD-BL-1T-ON-CC- 10S | 2917418 | 1 |
| Time range 3300 s | ETD-BL-1T-ON-CC-300S | 2917421 | 1 |
| Time range 0.330 min | ETD-BL-1T-ON-CC- 30MIN | 2917434 | 1 |
| Time range 3300 min | ETD-BL-1T-ON-CC-300MIN | 2917447 | 1 |
| Timer relay with spring-cage connection | | | |
| Time range 0.110 s | ETD-BL-1T-ON-CC- 10S-SP | 2917573 | 1 |
| Time range 3300 s | ETD-BL-1T-ON-CC-300S-SP | 2917586 | 1 |
| Time range 0.330 min | ETD-BL-1T-ON-CC- 30MIN-SP | 2917599 | 1 |
| Time range 3300 min | ETD-BL-1T-ON-CC-300MIN-SP | 2917609 | 1 |

3 Technical data

| Input data | | | |
|--|---|--|--|
| Input voltage range | 24 V DC (19,2 V DC30 V DC) | | |
| Time setting range ETD-BL-1T-ON-CC- 10S ETD-BL-1T-ON-CC-300S ETD-BL-1T-ON-CC-30MIN ETD-BL-1T-ON-CC-300MIN ETD-BL-1T-ON-CC-10S-SP ETD-BL-1T-ON-CC-300S-SP | 0.1 s 10 s 3 s 300 s 0.3 min 30 min 3 min 300 min 0.1 s 10 s 0.3 s 300 s | | |
| ETD-BL-1T-ON-CC-30MIN-SP ETD-BL-1T-ON-CC-300MIN-SP | 0.3 min 30 min 3 min 300 min | | |
| Function | ON-CC: With switch-on delay with control contact | | |
| Setting accuracy | ≤ 2.5 % (of scale end value) | | |
| Repeat accuracy | $\leq 0.5~\%$ (From the measuring range final value) | | |
| Nominal current typ. | 15 mA (Relay ON) 7 mA (Relay OFF) | | |
| Output data | | | |
| Contact type | 1 floating PDT | | |
| Output fuse | 6.3 A (fast-blow) | | |
| Switching capacity | 1500 VA (6 A / 250 V AC) | | |
| Control contact | | | |
| Control contact | Non-floating, terminals A1-B1 | | |
| Control pulse length | min. 50 ms | | |
| General data | | | |
| Service life mechanical | Approx. 2 x 10 ⁷ cycles | | |
| Service life, electrical | Approx. 2 x 10 ⁵ cycles at ohmic load, 1000 VA | | |
| Operating mode | 100% operating factor | | |
| Degree of protection | IP20 | | |
| Pollution degree | 2 (according to EN 50178) | | |
| Surge voltage category | III, safe isolation (according to EN 50178) | | |
| Rated insulation voltage | 300 V AC (according to EN 50178) | | |

| Impulse withstand voltage | 6 kV (According to EN 50178) |
|---|--|
| Inflammability class acc. to UL 94 | VO |
| Assembly | on TS 35 profile rail acc. to EN 60715 |
| Mounting position | Any |
| Width | 6.2 mm |
| Height | 86 mm |
| Length | 80 mm |
| Type of housing | Polyamide PA, self-extinguishing |
| Color | green |
| Connection data Screw connection | |
| Conductor cross section, solid | 0.14 mm ² 2.5 mm ² |
| Conductor cross section, stranded | 0.14 mm ² 2.5 mm ² |
| Stripping length | 8 mm |
| Connection data Spring-cage conn. | |
| Conductor cross section, solid | 0.14 mm ² 2.5 mm ² |
| Conductor cross section, stranded | 0.14 mm ² 2.5 mm ² |
| Stripping length | 8 mm |
| Ambient conditions | |
| Ambient temperature (operation) | -20 °C 65 °C |
| Ambient temperature (storage/transport) | -25 °C 80 °C |
| Permissible humidity (operation) | 15 % 85 % |
| Conformance / approvals | |
| Conformity | CE compliant |
| ATEX | □ II 3 G Ex nAC II T4 X |
| UL, USA / Canada | UL/C-UL listed UL 508 |
| GL | GL EMC 1 C |
| Conformance with EMC directive 2004/10 | 8/EC |
| Immunity to interference according to | EN 61000-6-2 |
| Emitted interference according to | EN 61000-6-4 |
| Conformance with LV directive 2006/95/E | C |
| | |

4 Block diagram



Electronic equipm. for electrical power installations according to

103616_en_02 PHOENIX CONTACT 3

EN 50178

5 Safety regulations and installation notes



WARNING: Risk of electric shock

Never carry out work when voltage is present.

Installation notes



The device is designed for installation in potentially explosive areas in zone 2.



Note: Installation, operation and maintenance may be carried out only by qualified electricians. Follow the specified installation instructions. When installing and operating the device, the applicable safety directives (including national safety directives), accident prevention regulations, as well as general technical regulations, must be observed. The technical data should be taken from this data sheet and the certificates (conformity assessment, other possible approvals).



Note: Do not open the device or make changes to it. Do not repair the device yourself, replace it with an equivalent device. Repairs may only be carried out by the manufacturer. The manufacturer is not liable for any damage due to violation of the described regulations.



Note: The IP20 degree of protection (EN 60529) of the device is intended for a clean and dry environment. Do not subject the device to any load that exceeds the described limits.



WARNING: Explosion hazard

The device has not been designed for use in potentially dust-explosive atmospheres.

Installation in Ex area (zone 2)



Note: Please observe the requirements defined for use in potentially explosive atmospheres!



WARNING: Explosion hazard

The device should be installed in a housing (control or distributor box) that fulfills the requirements of EN 60079-15 and at least IP54 (EN 60529) degree of protection.



WARNING: Explosion hazard

When installing and connecting the supply and signal circuits observe the requirements of EN 60079-14. Only devices suitable for operation in Ex zone 2 and the conditions at the application site may be connected to the circuits in zone 2.



WARNING: Explosion hazard

Cables may be connected and disconnected in potentially explosive areas only when power is disconnected.




WARNING: Explosion hazard

The device must be stopped and immediately removed from the Ex area if it is damaged or was subject to an impermissible load or stored incorrectly or if it malfunctions.



You can download the latest documents from www.phoenixcontact.net/download.

6 Structure



- 1 Knurled wheel for setting the time
- 2 LED U/t (green): Supply voltage and adjustable time
- 3 LED R (yellow): Output relay

7 Installation



WARNING: Risk of electric shock

Never carry out work when voltage is present.


The module can be snapped onto all 35 mm DIN rails according to EN 60715.

UL requirement: Use copper cables approved for at least 75°C.

Power supply

The module is supplied with 24 V of DC voltage.

8 Time setting



The time can be adjusted variably using a screwdriver (blade width 2.5 mm). The value set on the knurled wheel multiplied by 10 gives the percentage set value of the time end value.

Example:

Time end range of the time relay = 10 s

Setting on the knurled wheel = 6 6 x 10 % = 60 % Time end range of the time relay = 10 s 60 % of 10 s = 6 s

According to the setting of the knurled wheel (1...10), you can also read the time directly from the "Time setting for different time setting ranges" table.

Time settings for various time setting ranges:

| Position Knurled wheel | 0.1 - 10 s time [seconds] | 3 - 300 s time [seconds] | 0.3 - 30 min time [minutes] | 3 - 300 min time [minutes] |
|---------------------------|------------------------------|-----------------------------|--------------------------------|-------------------------------|
| 0 | 0,1 | 3 | 0,3 | 3 |
| 1 | 1 | 30 | 3 | 30 |
| 2 | 2 | 60 | 6 | 60 |
| 3 | 3 | 90 | 9 | 90 |
| 4 | 4 | 120 | 12 | 120 |
| 5 | 5 | 150 | 15 | 150 |
| 6 | 6 | 180 | 18 | 180 |
| 7 | 7 | 210 | 21 | 210 |
| 8 | 8 | 240 | 24 | 240 |
| 9 | 9 | 270 | 27 | 270 |
| 10 | 10 | 300 | 30 | 300 |



The following table shows some examples: All intermediate values (e. g. 1.5) can be adjusted. The smallest adjustable time is reached at position "0". No time can be set between "10" and "0". This area is identified with a quickly flashing geed LED.

9 Diagnostics

The LEDs indicate the following error states:


LED U/t (green, backlighting of the knurled wheel)

- Flashes: Voltage is present, the set time is elapsing
- Flashing quickly: Undefined time range between "10" and "0" adjusted
- On: Voltage is present, the set time has elapsed

LED R (yellow)

- On: The output relay has picked up
- Off: The output relay is dropped

10 Connection example



11 Function



ON-CC: With switch-on delay

Supply voltage U must be continuously applied to the device (green LED U/t lights up). When control contact A1-B1 closes, the set time t starts running (green LED U/t flashes). After time t has elapsed (green LED U/t lights up), the output relay picks up (yellow LED R lights up). This state remains until the control contact opens. If the control contact is opened before time t elapses, the elapsed time is deleted (relay does not pick up) and is restarted with the next cycle.