

## Roughing cutter, HSSE Co 8

4 cutting edges, TiCN-coated

**ORION**<sup>®</sup>

### Application:

End mill for universal use when plunge milling, groove milling and keyway cutting as well as face milling and peripheral milling.



### Execution:

- HSSE Co 8
- fine roughing teeth
- centre cutting (over diameter 20 mm without centre cutting)
- TiCN coating for long service life
- straight shank in accordance with DIN 1835 B

<b>Art. no.</b>	<b>15300 300</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	15300300
<b>Cutting material</b>	HSSE Co8
<b>Surface</b>	TiCN
<b>Type</b>	HR
<b>Number of cutting edges</b>	6 PCS
<b>Twist angle</b>	30°
<b>Edge protection chamfer length</b>	0.2 mm
<b>Tool holding device</b>	HB parallel shank
<b>Construction length</b>	Long
<b>Cutting edge diameter</b>	30 mm
<b>Cutting edge length</b>	90 mm
<b>Length</b>	166 mm
<b>Shank diameter</b>	25 mm
<b>fz steel 1300</b>	0.13 mm
<b>Gross Weight</b>	0.700 kg
<b>Product Group</b>	106

### EAN

4039247095056