


MCOB128064T1V-WP	128 x 64	White	OLED Module
<b>Specification</b>			
Version: 1	Date: 16/05/2017		
<b>Revision</b>			

Display Features			Box Quantity	Weight / Display
Resolution	128 x 64			
Appearance	White on Black			
Logic Voltage	3V			
Interface	Parallel			
Module Size	75.00 x 52.70 x 8.50 mm			
Operating Temperature	-40°C ~ +80°C			
Construction	COB	---	---	


\* - For full design functionality, please use this specification in conjunction with the SSD1309 specification. (Provided Separately)

Display Accessories	
Part Number	Description
MCC1A20DILP -20DILS-150	20 Way Dual in-line to Dual in-line connector cable.
VBWFD2	USB PIC18F2550 micro-controller board to 20 Way DIL COB graphic LCD.

Optional Variants	
Appearance	Voltage
Yellow on Black	

## Mechanical Specifications


Module Size	75.00 x 52.70 x 8.50 (With Backlight)				W x H x D mm
Viewing Area	57.01 x 29.49	W x H mm	Hole-to-Hole	70.00 x 49.70	W x H mm
Dot Size	0.40 x 0.40	W x H mm	Dot Pitch	0.43 x 0.43	W x H mm



MCOB128064T1V-WP	128 x 64	White	OLED Module
Version: 1		Date: 16/05/2017	
Revision			

## Pin Layout

Pin	Symbol	Description
1	VDD	Power Supply Pin for core logic operation.
2	VSS	Ground.
3	NC	No Connection.
4~11	D0~D7	Data Bus.
12	CS	Chip Select Input, connecting to MCU. Chip is enabled for MCU communication when CS# is pulled Low.
13	NC	No Connection
14	/RES	Reset Signal Input. Initialisation for chip is executed when pulled Low. Keep pulled High during normal operation.
15	R/W	Read / Write control input pin, connecting to MCU. 8080 Mode= Pin is pulled Low and the chip selected.
16	D/C	Data / Command control pin connecting to the MCU.
17	E	This pin is MCU interface input. 8080 Mode= Pin is pulled Low and the chip selected.
18	NC	No Connection.
19	DISP	Display Off.
20	NC	No Connection.



MCOB128064T1V-WP	128 x 64	White	OLED Module
<b>Specification</b>			
Version: 1		Date: 16/05/2017	
<b>Revision</b>			

Absolute Maximums Ratings					
Item	Symbol	Minimum	Typical	Maximum	Unit
Supply Voltage for Logic	VDD	-0.30	---	4.00	V
Operating Temperature	Vopr	-40	---	80	°C
Storage Temperature	Vstg	-40	---	80	°C

Electronic Characteristics						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
Input High Voltage	VIH	---	0.80	---	VDD	V
Input Low Voltage	VIL	---	GND	---	0.20	V
Output High Voltage	VOH	---	0.90	---	VDD	V
Output Low Voltage	VOL	---	GND	---	0.10	V
Supply Voltage for Logic	VDD	---	2.80	3.00	3.30	V
50% Checkboard Operating Current.	IDD	VDD=3.0V	105	110	130	mA

OLED Characteristics						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
Viewing Angle	(V) $\theta$	---	160	---	---	Deg
	(H) $\phi$	---	160	---	---	Deg
Contrast Ratio	CR	Dark	2000:1	---	---	---
Response Time	T Rise	---	---	10	---	$\mu$ s
	T Fall	---	---	10	---	$\mu$ s
Display with 50% Checkboard Brightness			60	70	---	cd/m <sup>2</sup>
CIE <sub>x</sub> (Yellow)		(CIE1931)	0.26	0.28	0.30	---
CIE <sub>y</sub> (Yellow)		(CIE1931)	0.30	0.32	0.34	---

OLED Life Time			
Item	Conditions	Typical	Remark
Operating Life Time	Ta=25°C. Initial checkboard brightness, 50%.	20,000 Hours	---

MCOB128064T1V-WP	128 x 64	White	OLED Module
<b>Specification</b>			
Version: 1		Date: 16/05/2017	
<b>Revision</b>			