

Torque wrench

DREMOMETER with calibration certificate according to DIN EN ISO 6789



Application:

The tightening value is set and read from the scale by means of rotary motion with angle key integrated in the handle end.



Execution:

- Audible and perceptible release when the tightening torque is reached
- Single key, one arm, with automatic release

Advantage:

- Special design ensures faultless operation
- The measured value or set torque is not changed
- Independent of handle position

Art. no.	52248 040
Brand	GEDORE
Manufacturer Part Number	7670 180
Min. torque	155 Nm
Max. torque	760 Nm
Min./max. torque	155-760 Nm
Scale value torque	5 Nm
Tip size	3/4 inch
Error limit (%)	3 %
Min./max. length	812-1413 mm
Calibration certificate	Yes
ISO	6789
Gross Weight	4.200 kg
Product Group	556

EAN

4002805863015