

Thermistor motor prot. relay Standard evaluation unit  
 17.5 mm enclosure Screw terminals 1 NO contact, 1 NC  
 contact US = 24-240 V AC/DC Auto RESET Suitable for  
 bimetal switches 2 LEDs (READY/TRIPPED) Galvanic  
 separation



Figure similar

Article number		
<b>Product brand name</b>		SIRIUS
<b>Product category</b>		SIRIUS 3RN2 thermistor motor protection
<b>Product designation</b>		Thermistor motor protection relay
<b>Product type designation</b>		3RN2

General technical data

<b>Display version LED</b>		Yes
<b>Power loss [W] for rated value of the current</b>		
• at AC in hot operating state	W	0.9
• at DC in hot operating state	W	0.9
<b>Insulation voltage</b>		
• for overvoltage category III according to IEC 60664		
— with degree of pollution 3 rated value	V	300
<b>Degree of pollution</b>		3
<b>Surge voltage resistance rated value</b>	kV	4
<b>Protection class IP</b>		IP20
<b>Shock resistance</b>		

<ul style="list-style-type: none"> <li>• acc. to IEC 60068-2-27</li> </ul>		11g / 15 ms
<b>Vibration resistance</b>		
<ul style="list-style-type: none"> <li>• acc. to IEC 60068-2-6</li> </ul>		10 ... 55 Hz: 0.35 mm
<b>Mechanical service life (switching cycles)</b>		
<ul style="list-style-type: none"> <li>• typical</li> </ul>		10 000 000
<b>Electrical endurance (switching cycles)</b>		
<ul style="list-style-type: none"> <li>• at AC-15 at 230 V typical</li> </ul>		100 000
<b>Thermal current of the switching element with contacts maximum</b>	A	5
<b>Equipment marking</b>		
<ul style="list-style-type: none"> <li>• acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750</li> </ul>		K
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> </ul>		K
<ul style="list-style-type: none"> <li>• acc. to DIN EN 81346-2</li> </ul>		K

### Control circuit/ Control

<b>Type of voltage of the control supply voltage</b>		AC/DC
<b>Control supply voltage at AC</b>		
<ul style="list-style-type: none"> <li>• at 50 Hz rated value</li> </ul>	V	24 ... 240
<ul style="list-style-type: none"> <li>• at 60 Hz rated value</li> </ul>	V	24 ... 240
<b>Control supply voltage at DC</b>		
<ul style="list-style-type: none"> <li>• rated value</li> </ul>	V	24 ... 240
<b>Operating range factor control supply voltage rated value at DC</b>		
<ul style="list-style-type: none"> <li>• initial value</li> </ul>		0.85
<ul style="list-style-type: none"> <li>• Full-scale value</li> </ul>		1.1
<b>Operating range factor control supply voltage rated value at AC at 50 Hz</b>		
<ul style="list-style-type: none"> <li>• initial value</li> </ul>		0.85
<ul style="list-style-type: none"> <li>• Full-scale value</li> </ul>		1.1
<b>Operating range factor control supply voltage rated value at AC at 60 Hz</b>		
<ul style="list-style-type: none"> <li>• initial value</li> </ul>		0.85
<ul style="list-style-type: none"> <li>• Full-scale value</li> </ul>		1.1
<b>Inrush current peak</b>		
<ul style="list-style-type: none"> <li>• at 24 V</li> </ul>	A	0.3
<ul style="list-style-type: none"> <li>• at 240 V</li> </ul>	A	8
<b>Duration of inrush current peak</b>		
<ul style="list-style-type: none"> <li>• at 24 V</li> </ul>	ms	0.15
<ul style="list-style-type: none"> <li>• at 240 V</li> </ul>	ms	0.15

### Measuring circuit

<b>Buffering time in the event of power failure minimum</b>	ms	40
---	----	----

### Precision

Relative metering precision	%	9
-----------------------------	---	---

### Auxiliary circuit

Material of switching contacts		AgSnO2
Number of NC contacts		1
<ul style="list-style-type: none"> <li>• for auxiliary contacts</li> </ul>		
Number of NO contacts		1
<ul style="list-style-type: none"> <li>• for auxiliary contacts</li> </ul>		
Number of CO contacts		0
<ul style="list-style-type: none"> <li>• for auxiliary contacts</li> </ul>		
Operating current of auxiliary contacts at DC-13		
<ul style="list-style-type: none"> <li>• at 24 V</li> </ul>	A	1
<ul style="list-style-type: none"> <li>• at 125 V</li> </ul>	A	0.2
<ul style="list-style-type: none"> <li>• at 250 V</li> </ul>	A	0.1

### Main circuit

Operating frequency rated value	Hz	50 ... 60
---------------------------------	----	-----------

### Outputs

Ampacity of the output relay at AC-15		
<ul style="list-style-type: none"> <li>• at 250 V at 50/60 Hz</li> </ul>	A	3
Ampacity of the output relay at DC-13		
<ul style="list-style-type: none"> <li>• at 24 V</li> </ul>	A	1
<ul style="list-style-type: none"> <li>• at 125 V</li> </ul>	A	0.2
Continuous current of the DIAZED fuse link of the output relay	A	6

### Electromagnetic compatibility

Conducted interference		
<ul style="list-style-type: none"> <li>• due to burst acc. to IEC 61000-4-4</li> </ul>		2 kV (power ports) / 1 kV (signal ports)
<ul style="list-style-type: none"> <li>• due to conductor-earth surge acc. to IEC 61000-4-5</li> </ul>		2 kV (line to ground)
<ul style="list-style-type: none"> <li>• due to conductor-conductor surge acc. to IEC 61000-4-5</li> </ul>		1 kV (line to line)
Electrostatic discharge acc. to IEC 61000-4-2		6 kV contact discharge / 8 kV air discharge

### Galvanic isolation

Design of the electrical isolation		galvanic
Galvanic isolation		
<ul style="list-style-type: none"> <li>• between entrance and outlet</li> </ul>		Yes
<ul style="list-style-type: none"> <li>• between the outputs</li> </ul>		Yes
<ul style="list-style-type: none"> <li>• between the voltage supply and other circuits</li> </ul>		Yes

### Connections/Terminals

Product function		
------------------	--	--

<ul style="list-style-type: none"> <li>removable terminal for auxiliary and control circuit</li> </ul>		Yes
<b>Type of electrical connection</b>		screw-type terminals
<b>Type of connectable conductor cross-sections</b>		1x (0.5 ... 4.0 mm <sup>2</sup> ), 2x (0.5 ... 2.5 mm <sup>2</sup> ) 1x (0.5 ... 4 mm <sup>2</sup> ), 2x (0.5 ... 1.5 mm <sup>2</sup> ) 1x (20 ... 12), 2x (20 ... 14)
<b>Connectable conductor cross-section</b>		
<ul style="list-style-type: none"> <li>solid</li> </ul>	mm <sup>2</sup>	0.5 ... 4
<ul style="list-style-type: none"> <li>finely stranded with core end processing</li> </ul>	mm <sup>2</sup>	0.5 ... 4
<b>AWG number as coded connectable conductor cross section</b>		
<ul style="list-style-type: none"> <li>solid</li> </ul>		20 ... 12
<ul style="list-style-type: none"> <li>stranded</li> </ul>		20 ... 12
<b>Tightening torque</b>		
<ul style="list-style-type: none"> <li>with screw-type terminals</li> </ul>	N·m	0.6 ... 0.8

### Installation/ mounting/ dimensions

<b>Mounting position</b>		any
<b>Mounting type</b>		screw and snap-on mounting onto 35 mm standard mounting rail
<b>Height</b>	mm	100
<b>Width</b>	mm	17.5
<b>Depth</b>	mm	90
<b>Required spacing</b>		
<ul style="list-style-type: none"> <li>with side-by-side mounting <ul style="list-style-type: none"> <li>— forwards</li> <li>— Backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> <li>for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— Backwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>for live parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— Backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul>	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0
	mm	0

## Ambient conditions

<b>Installation altitude at height above sea level</b>		
• maximum	m	2 000
<b>Ambient temperature</b>		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +85
• during transport	°C	-40 ... +85
<b>Relative humidity</b>		
• during operation	%	70

## Certificates/approvals

<b>General Product Approval</b>	<b>EMC</b>	<b>For use in hazardous locations</b>	<b>Declaration of Conformity</b>
---------------------------------	------------	---------------------------------------	----------------------------------



<b>Test Certificates</b>	<b>Marine / Shipping</b>	<b>other</b>
--------------------------	--------------------------	--------------

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Environmental Confirmations](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3RN2010-1CW30>

**Cax online generator**





<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RN2010-1CW30>


**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3RN2010-1CW30>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3RN2010-1CW30&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3RN2010-1CW30&lang=en)





last modified:

09/25/2017