Monitoring Relays 1-Phase True RMS AC/DC Over or Under Current Types DIB01, PIB01



PIB01

can be used to avoid relay

operation when not desired

The LED's indicate the state

of the alarm and the output

relay. Through the built-in

shunt it is possible to moni-

tor loads up to 10 A AC/DC.

(maintenance, transitions).

- TRMS AC/DC over or under current monitoring relay
- Current measuring through internal shunt
- Selection of measuring range by DIP-switches
- Measuring ranges from 0.1 mA to 10 A AC/DC
- Adjustable current on relative scale
- Adjustable hysteresis on relative scale
 Adjustable delay function (0.1 to 30 s)
- Programmable latching or inhibit at set level
- Output: 8 A SPDT relay N.D. or N.E. selectable
- For mounting on DIN-rail in accordance with
- DIN/EN 50 022 (DIB01) or plug-in module (PIB01) • 22.5 mm Euronorm housing (DIB01)
- or 36 mm plug-in module (PIB01)
- LED indication for relay, alarm and power supply ON
- Galvanically separated power supply

Product Description

DIB01

DIB01 and PIB01 are precise TRMS AC/DC over or under current (selectable by DIPswitch) monitoring relays. Direct measuring or through current transformer.

Owing to the built-in latch function, the ON-position of the relay output can be maintained. Inhibit function

Type Selection

Mounting	Output	Measuring range	Supply: 24 to 48 VAC/DC	Supply: 115/230 VAC
DIN-rail	SPDT	0.1 to 5 mA AC/DC 1 to 50 mA AC/DC 10 to 500 mA AC/DC 0.1 to 5 A AC/DC 1 to 10 A AC/DC	DIB 01 C D48 5mA DIB 01 C D48 50mA DIB 01 C D48 500mA DIB 01 C D48 5A DIB 01 C D48 5A DIB 01 C D48 10A	DIB 01 C B23 5mA DIB 01 C B23 50mA DIB 01 C B23 500mA DIB 01 C B23 500mA DIB 01 C B23 5A DIB 01 C B23 10A
Plug-in	SPDT	0.1 to 5 mA AC/DC 1 to 50 mA AC/DC 10 to 500 mA AC/DC 0.1 to 5 A AC/DC 1 to 10 A AC/DC	PIB 01 C D48 5mA PIB 01 C D48 50mA PIB 01 C D48 500mA PIB 01 C D48 500mA PIB 01 C D48 5A PIB 01 C D48 10A	PIB 01 C B23 5mA PIB 01 C B23 50mA PIB 01 C B23 500mA PIB 01 C B23 5A PIB 01 C B23 10A

Input Specifications

Input (current level)			Measuri	ng ranges (cont.)		
DIB01	Terminals Y1, Y2				Internal resist.	Max. curr.
PIB01	Terminals 5, 7		500M	A:10 to 100 mA AC/DC	0.5 Ω	700 mA
Measuring ranges				20 to 200 mA AC/DC	0.5 Ω	700 mA
Direct	Internal resist.	Max. curr.		50 to 500 mA AC/DC	0.5 Ω	700 mA
Selectable by DIP-switch				Max. current for 1 s		1.4 A
5MA: 0.1 to 1 mA AC/DC	50 Ω	50 mA	5A:	0.1 to 1 A AC/DC	0.05 Ω	6 A
0.2 to 2 mA AC/DC	50 Ω	50 mA		0.2 to 2 A AC/DC	0.05 Ω	6 A
0.5 to 5 mA AC/DC	50 Ω	50 mA		0.5 to 5 A AC/DC	0.05 Ω	6 A
Max. current for 1 s		100 mA		Max. current for 1 s		15 A
50MA: 1 to 10 mA AC/DC	5 Ω	150 mA	10A:	1 to 10 A AC/DC	$3 \text{ m}\Omega$	11 A
2 to 20 mA AC/DC	5Ω	150 mA		Max. current for 1 s		50 A
5 to 50 mA AC/DC	5 Ω	150 mA				
Max. current for 1 s		500 mA				

Ordering Key DIB 01 C B23 5A

Housing	
Function	
Туре	
Item number	
Output	
Power supply —	
Measuring range ——	





Input Specifications (cont.)

Measuring ranges (cont.)			
Standard CT (examples) TADK2 50 A/5 CTD1 150 A/5 CTD4 400 A/5 TAD12 1000 A/5 TACO200 6000 A/5	A 5 A 1 A 2 A 1	AAC _{rms} 5 to 50 A 15 to 150 A 40 to 400 A 100 to 1000 A 600 to 6000 A	Max. curr. 60 A 180 A 480 A 1200 A 7200 A
Note: The input voltage cannot raise over 300 VAC/DC w respect to ground (PIB01 c			
Contact input DIB01 PIB01 Disabled Enabled Latch disable	ר : •	Terminals Z1, Y1 Terminals 8, 9 > 10 k Ω < 500 Ω > 500 ms	

Output Specifications

Output Rated insulation voltage	SPDT relay 250 VAC
Trated insulation voltage	200 VAC
Contact ratings (AgSnO ₂)	μ
Resistive loads AC 1	8 A @ 250 VAC
DC 12	5 A @ 24 VDC
Small inductive loads AC 15	2.5 A @ 250 VAC
DC 13	2.5 A @ 24 VDC
Mechanical life	\geq 30 x 10 ⁶ operations
Electrical life	$\geq 10^5$ operations
	(at 8 A, 250 V, $\cos \varphi = 1$)
Operating frequency	≤ 7200 operations/h
Dielectric strength	
Dielectric voltage	\geq 2 kVAC (rms)
Rated impulse withstand volt.	4 kV (1.2/50 µs)
	····· (·· <u>-</u> / •• p.e/

Supply Specifications

Power supply Rated operational voltage through terminals:	Overvoltage cat. III (IEC 60664, IEC 60038)	
A1, A2 or A3, A2 (DIB01) 2, 10 or 11, 10 (PIB01) D48: B23:	24 to 48 VAC/DC ± 15% 45 to 65 Hz, insulated 115/230 VAC ± 15% 45 to 65 Hz, insulated	
Dielectric voltage Supply to input Supply to output Input to output	DC supply AC supply 2 kV 4 kV 4 kV 4 kV 4 kV 4 kV 4 kV 4 kV	
Rated operational power AC DC	4 VA 3 W	

General Specifications

Power ON delay		$1 s \pm 0.5 s \text{ or } 6 s \pm 0.5 s$		
Reaction time Alarm ON delay Alarm OFF delay		(input signal variation from -20% to +20% or from +20% to -20% of set value) < 100 ms < 100 ms		
Accuracy		(15 min warm-up time)		
Temperature drift		± 1000 ppm/°C		
Delay ON alarm Repeatability		\pm 10% on set value \pm 50 ms \pm 0.5% on full-scale		
Indication for				
Power supply ON		LED, green		
Alarm ON		LED, red (flashing 2 Hz during delay time)		
Output relay ON		LED, yellow		
Environment		(EN 60529)		
Degree of protection	۱	IP 20		
Pollution degree		3 (DIB01), 2 (PIB01) -20 to 60°C, R.H. < 95%		
Operating temperating Storage temperature		-20 to 80°C, R.H. < 95%		
Housing	-			
Dimensions	DIB01	22.5 x 80 x 99.5 mm		
	PIB01	36 x 80 x 94 mm		
Weight		Approx. 150 g		
Screw terminals				
Tightening torque		Max. 0.5 Nm		
Annevala		acc. to IEC 60947		
Approvals		UL, CSA		
CE Marking		Yes		
EMC		Electromagnetic Compatibility		
Immunity Emission		According to EN 61000-6-2 According to EN 61000-6-3		



Mode of Operation

DIB01 and PIB01 monitor both AC and DC over or under current through an internal shunt.

Example 1

(connection between terminals Z1, Y1 or 8, 9 - latching function enabled)

The relay operates and latches in operating position when the measured value

exceeds (or drops below) the set level for more than the set delay time. Provided that the current has dropped below (or has exceeded) the set point (see hysteresis setting), the relay releases when the interconnection between terminals Z1, Y1 or 8, 9 is interrupted or the power supply is interrupted as well. The red LED flashes until the delay time has expired or the measured value comes back to a non-alarm value (see hysteresis setting).

Example 2 (Stardard CT)

(no connection between terminals Z1, Y1 or 8, 9 - latch function disabled)

The relay operates when the measured value exceeds (or drops below) the set level for

more than the set delay time. It releases when the current drops below (or exceeds) the set level (see hysteresis setting) or when power supply is interrupted.

Note

When the inhibit contact is opened, if the input signal is already in alarm position, the delay time needs to elapse before relay activation.

Function/Range/Level and Time Delay Setting

Adjust the input range setting the DIP switches 1 and 2 as shown below (except for models DIB01xxx10A and PIB01xxx10A). Select the desired function setting the DIP switches 3 to 6 (1 to 4 for DIB01xxx10A and PIB01xxx10A) as shown below. To access the DIP switches open the grey plastic cover as shown below.


Selection of level and time delay:

Upper knob:

Setting of hysteresis on relative scale: 0 to 30% on set value.

Centre knob:


Current level setting on relative scale: 10 to 110% on full scale. **Lower knob:** Setting of delay on alarm time on absolute scale (0.1 to 30 s).






Operation Diagrams


Over current - N.D. relay




Under current - Latch function - N.D. relay




Under current - N.D. relay





Wiring Diagrams



CARLO GAVAZZI

Dimensions

