



## Technical Data Sheet

### SX Contractors Silicone GP Acetoxy general purpose silicone



#### Product Description

An acetoxy curing general purpose silicone which provides a permanently water tight flexible seal and offers good adhesive properties, making it suitable for use on glass, most painted surfaces, sanitary ware, ceramics and most non-porous surfaces.

#### Benefits

- Versatile sealant
- High elasticity
- Good resistance to UV, water and weather

#### Applications

Perimeter sealing around most types of door and window frames and seals glass to glass. Seals around pipes, sanitary fixtures and duct work.

#### Directions Of Use

Cut the cartridge seal and screw on the nozzle which should be cut to your required size. Using a skeleton gun, apply the sealant into the gap ensuring a good solid fill. If required, place masking tape along edges, removing within 5 minutes of application. In deep joints reduce the joint depth to 50% of the joint width using expanding foam or joint backer rod.

#### Additional information

100 % modulus	DIN 53504 S2	0,30 N/mm <sup>2</sup>
Application rate	@ Ø3 mm/6,3 bar	700 g/min
Application temperature		+5 °C to +40 °C
Base		Silicone
Curing time	@ +23 °C/50% RH	2mm/24 hours
Density	ISO 1183-1	0,96 g/ml
Elongation at break	DIN 53504 S2	440%
Flow	ISO 7390	< 2 mm
Frost resistance during transportation		Up to -15 °C
Shorea hardness	DIN 53505	17
Skin formation	DBTM 16	10-12 minutes @ +23 °C/50% RH
Temperature resistance		-40 °C to +180 °C
Tensile strength	DIN 53504 S2	1,30 N/mm <sup>2</sup>
Viscosity		40

*These are typical values*

#### Limitations

- Not suitable for PE, PP, PC, PMMA, PTFE, soft plastics, neoprene and bituminous substrates
- Not suitable for applications on concrete, marble, lead, copper and galvanized steel

#### Surface Preparations and Finishing

Surfaces must be clean, dry and free of dust, grease and other loose material. Adhesion tests prior to application are recommended. Always tool within 5 minutes of application and use a spatula or stick wet with soapy water.

#### Paintability

This product is not paintable.



## Technical Data Sheet

### SX Contractors Silicone GP Acetoxy general purpose silicone

#### Cleaning

Cured material can only be mechanically removed. Hands can be cleaned with SX Multi-Purpose Cleaning Wipes. Issue 4/29.04.16/0067.11.DB

#### Colour(s)

- Clear
- White

#### Packaging


- Cartridge

*For product specifications, please refer to the Product Detail Page*

#### Shelf Life

If kept stored in a cool, dry place, in unopened original packaging, between +5°C and +25°C, shelf life is up to 18 months from production date.

#### Certifications

	A+ French VOC Regulation
	EN 15651-1: F-EXT-INT-CC EN 15651-2: G-CC EN 15651-3: S S1

#### Health & Safety

Product Safety Data Sheet must be read and understood before use. These are available on request and via the Den Braven websites.

#### Warranty & Guarantee

Den Braven warrants that its product complies, within its shelf life, to its specification.

#### Disclaimer

All information in this document and in all our other publications (including electronic ones) is based on our current knowledge and experience and is the exclusive (intellectual) property of Den Braven. No part of this document may be copied, shown to third parties, reproduced, communicated to the public or used in any other way without Den Braven's written consent. The technical information in this document serves as an indication and is non-exhaustive. Den Braven is not liable for any damage, either direct or indirect, due to (editorial) errors, incompleteness and/or incorrectness of this document. This includes, but is not limited to, incompleteness and/or incorrectness due to technological changes or any research conducted between the date of publication of this document and the date on which the product is acquired. Den Braven reserves the right to amend the wording of this document. Den Braven cannot be held liable for any damage, either direct or indirect, due to the use of the product depicted in this document. The user must read and understand the information in this document and other documents relating to the products prior to the use the product. The user is responsible for performing all the requisite tests to make sure that the product is suitable for its intended use. We have no influence in what

way the product is applied and/or any circumstances relating to events occurring during storage or transport and therefore we do not accept any liability for damage. All deliveries are made exclusively in accordance with our general terms of conditions which have been filed at the Dutch Chamber of Commerce.