



MicroThan®

VIBROTHAN®

## TEGERA® 9180

Anti-vibration glove, unlined, Microthan®, Vibrothan®, polyester, Cat. II, black, grey, yellow, reinforced index finger, reinforced fingertips, chrome free, Velcro®, for heavy work

### PROPERTIES

Flexible, good grip, good fit, extra comfortable

### SPECIFICATION

TYPE OF GLOVE Anti-vibration gloves

CATEGORY Cat. II

SIZE RANGE (EU) 7, 8, 9, 10, 11, 12

PALM MATERIAL Microthan®, Vibrothan®

BACK MATERIAL Polyester

LINING Unlined

DEXTERITY 5

FASTENING Velcro®

LENGTH RANGE 210-242 mm

COLOUR Black, grey, yellow

PAIRS PER PACKAGE/CARTON 6/60

DISPLAY Hook with hangtag

MATERIAL SPECIFICATION Polyurethane, natural latex, polyester, nylon

1(3)

## TEGERA® 9180

### FEATURES

Vibration-reducing according to EN ISO 10819, chrome free, reinforced index finger, reinforced seams, reinforced fingertips, padded palm, pre-curved fingers, specially designed thumb, short model, ergonomically shaped, specially designed details

### PRIMARY PROTECTION

Prevents risk of: chrome allergy, vibration injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt

### PRIMARY ENVIRONMENTS OF USE

Harsh environments

### PRIMARY INDUSTRIES OF USE

Mining, machinery and equipment, MRO, automotive, building and construction

### TYPE OF WORK

Heavy weight



CE Cat. II

EN 388:2003 0222 EN ISO 10819:2013



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-01-04

2(3)

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

## TEGERA® 9180

### EC TYPE EXAMINATION

Notified Body: 0321 SATRA Technology Centre, Wyndham Way, Telford Way, Kettering, Northamptonshire, NN16 8SD, United Kingdom

### COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	0	(4)
B) Resistance to cutting (Index)	2	(5)
C) Tear resistance (Newton)	2	(4)
D) Puncturing resistance (Newton)	2	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2000	8000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	

EN ISO 10819:2013 Mechanical vibration and shock. Hand-arm vibration. Measurement and evaluation of the vibration transmissibility of gloves at the palm of the hand



CE Cat. II

EN 388:2003 EN ISO 10819:2013  
0222



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-01-04

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com