

## Type ER precision collet chuck

GERC-B, DIN 6499/ISO 15488-B, concentricity of 5 µm

**FAHRION®**  
FAIR BEYOND PRECISION

### Application:

For clamping tools with straight shank.

### Execution:


- For ATORN precision collet chucks and Fahrion CentroP precision spring collet chucks.
- With FAHRION|Protect corrosion protection for longer service life.
- Surface super-finished for enhanced retention force.

### Advantage:

- Collets do not need to be replaced as often or can be used longer for specific applications.
- Greater concentricity extends tool service life.

### Delivery:

1x type ER precision collet chuck.



<b>Art. no.</b>	<b>23322 584</b>
<b>Brand</b>	FAHRION
<b>Manufacturer Part Number</b>	13716011800
<b>Collet type</b>	470E GERC32-B
<b>Clamping diameter</b>	18 mm
<b>Min./max. clamping range</b>	3-20 mm
<b>Outer diameter</b>	33 mm
<b>Length</b>	40 mm
<b>Clamping bypass</b>	-1 mm
<b>Gross Weight</b>	0.117 kg
<b>Product Group</b>	235

### EAN

4054631179570