

T-slot bolts



Application:

For clamping workpieces on machine tables.

Version:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 435
DIN	787
Thread dimension	M12
Groove width	14 mm
Length excluding head	100 mm
Outer diameter	13.7 mm
Thread length	65 mm
Length of head	22 mm
Head height	8 mm

EAN-Code

4020772082970