

Micrometer

with disc-shaped measuring faces

Mitutoyo

Application:

For measuring tooth span on cogs, for recesses, groove distances etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Including box, set normal



Art. no.	32016 643
Brand	MITUTOYO
Manufacturer Part Number	123-106
Min./max. length measuring range	125-150 mm
Vernier scale	0.01 mm
Measuring surface diameter	30 mm
Measuring spindle increments	0.5 mm
Bracket depth	94 mm
Spindle clamping	Yes
Error limit	7 µm
Display	Nonius
Min./max. measurement force	0.7-11 N
Calibration Group	D
Gross Weight	1.370 kg
Product Group	3MA

EAN

4946368013046