









Die-cast heatsinks

Die-cast acc. to german standard DIN 41882

– other lengths and drillings on request

art. no.			
			
K 3 ...		for mounting use insulator: art. no.: IS 53	
please indicate:		... semiconductor retaining thread M 6, M 8, M 10, M 12, 1/4"-28 UNF	
art. no.			
			
K 3 T ...		Cathode lug insulator with an additional insulated connection (M 3). for mounting use insulator: art. no.: IS 53	
please indicate:		... semiconductor retaining thread M 6, M 8	
art. no.			
			
K 5 ...		for mounting use insulator: art. no.: IS 53	
please indicate:		... semiconductor retaining thread M 5, M 6, M 8, 1/4"-28 UNF	
art. no.			
			
K 9 ...			
please indicate:		... semiconductor retaining thread M 4, M 5	
surface:		black lacquered	

Mounting for TO 3 angle
Order example
Standard aluminium profiles
Heatsinks for PCB

→ A 123 Heatsinks for DC/DC converter
→ A 21 Profiles for lock-in fixing spring
→ A 133 – 134 Heatsink profile-overview
→ A 89 – 111 Technical introduction

→ A 112 – 113
→ A 84 – 88
→ A 13 – 17
→ A 2 – 7