



INFEED ON LEFT OR RIGHT, CONNECTION MAIN CIRCUIT: SPRING-LOADED TERMINAL, TERMINAL MAX. 25 MM<sup>2</sup>

General technical data:		
product brand name		SIRIUS
Product designation		infeed left or right
Protection class IP		IP20
Degree of pollution		3
Installation altitude at height above sea level maximum	m	2 000
Ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operation	°C	-20 ... +60
Vibration resistance		f = 4 to 5.8 Hz; d = 15 mm; f = 5.8 to 500 Hz; a = 2 m / s <sup>2</sup> 10 cycles
Shock resistance		Semi-sinusoidal a = 6 m/s <sup>2</sup> at 10 ms; 3 pos. and 3 neg. Shock in all axes
Equipment marking acc. to DIN EN 61346-2		W
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		W

Main circuit:		
Operating current with AC at 400 V Rated value	A	63
Operating voltage at AC-3 Rated value maximum	V	690










Installation/ mounting/ dimensions:		
Mounting type		screw and snap-on mounting
Width	mm	27
Height	mm	154

Depth	mm	107
-------	----	-----

### Connections/ Terminals:

Type of electrical connection for main current circuit		spring-loaded terminals
<b>Wire stripping length for main contacts</b>	mm	23
Connectable conductor cross-section for supply for main contacts using the upper clamping point		
• solid	mm <sup>2</sup>	4 ... 35
• stranded	mm <sup>2</sup>	4 ... 35
• finely stranded with core end processing	mm <sup>2</sup>	4 ... 25
• finely stranded without core end processing	mm <sup>2</sup>	6 ... 25
AWG number as coded connectable conductor cross section for supply for main contacts		
• using the upper clamping point		10 ... 3
Type of connectable conductor cross-section for supply for main contacts using the upper clamping point		
• solid		4 ... 35 mm <sup>2</sup>
• stranded		4 ... 35 mm <sup>2</sup>
• finely stranded with core end processing		4 ... 25 mm <sup>2</sup>
• finely stranded without core end processing		6 ... 25 mm <sup>2</sup>
Type of connectable conductor cross-section for AWG conductors for supply for main contacts		
• using the upper clamping point		10 ... 3

### Certificates/ approvals:

General Product Approval	EMC	Shipping Approval			
 UL					 LRS
Shipping Approval	other				
 PRS	 RINA	 RMRS	<a href="#">Declaration of Conformity</a>	<a href="#">Environmental Confirmations</a>	<a href="#">other</a>

### Safety related data:

Protection against electrical shock	finger-safe
-------------------------------------	-------------

### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA68305AC>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RA68305AC/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RA68305AC&lang=en>



last modified:

09.03.2015