

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936268520](#)

**Status:** **Active**

**Overview:** [Magnetic Jacks](#)

**Description:** MXMag Gigabit Ethernet 8 Core Non-PoE Single-Port RJ45 Connector, 21.40mm Depth, 3.30mm Phy Pin Length, Right-Angle, Standard Profile, with Shield Tabs, Non-LED, Industrial Temperature, with 2kV Shield Connection, Tray

**Documents:**

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[3D Model](#)

[Product Specification 934620001-N \(PDF\)](#)

[Packaging Specification 934620001-K \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Modular Jacks/Plugs
Series	<a href="#">93626</a>
Component Type	PCB Jack
Depth	21.40mm
Magnetic	Yes
Overview	<a href="#">Magnetic Jacks</a>
Performance Category	1000Mb
Power over Ethernet (PoE)	Non-PoE
Product Name	Magnetic Jack, MXMag, RJ45
Taxonomy	Modular Jacks and Plugs
UPC	889056690317

**Physical**

Color - Resin	Black
Durability (mating cycles max)	2500
Inverted / Top Latch	No
Jack Height	14.10mm
Keying to Mating Part	None
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	6.752/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	Spring Tabs
Plating min - Mating	0.051µm (Au), 1.016µm (PdNi)
Port Configuration	1x1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	0.5A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 7(c)-I**

**REACH SVHC**

Not Contained Per - D(2022)4187-DC (10 June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[93626 Series](#)

**Mates With**

IEC 60603 / TIA-1096-A

Voltage - Maximum

125V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

934620001-K

Product Specification

934620001-N

Sales Drawing

936260002-000

This document was generated on 10/26/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**