

Crimp Information Sheet

Terminal Part Number: 15344866
 Surface Plating: SN
 Material Thickness [mm]: 0,38
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,30 - 2,10
 Seal(s): 15324974 | 15324976

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50 / 15324974		1,50	80	1,30	0,05	2,05	0,10	4,10	0,10	4,15	0,10
2010 0,75 / 15324974		1,75	120	1,40	0,05	2,10	0,10	4,20	0,10	4,15	0,10
2010 0,75 / 15324976		1,75	120	1,40	0,05	2,10	0,10	4,20	0,10	4,15	0,10
2010 1,00 / 15324976		1,95	160	1,50	0,05	2,10	0,10	4,30	0,10	4,20	0,10
2010 1,00 / 15324974		1,95	160	1,50	0,05	2,10	0,10	4,30	0,10	4,20	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B

Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN

