






4.3-10 MALE TERMINATION 4 GHZ 2W SCREW

PAGE 1/2 ISSUE 27-11-15A SERIES PART NUMBER R4041D1000











COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL 2
Center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL 2
Outer contact	-	-
Insulator	PTFE	
Gasket	EPDM	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	-	-





4.3-10 MALE TERMINATION 4 GHZ 2W SCREW

PAGE 2/2	ISSUE 27-11-15A	SERIES TERMINATION	PART NUMBER R4041D1000
-----------------	------------------------	-----------------------	------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC -4
V.S.W.R (≤)	1.15

Operating Frequency Range	DC - 4	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	500	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	4.3-10	Male	IEC 60169-54
Weight	52,5000 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-40/+85	°C
Storage temperature range	-40/+85	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

IP 67 when mated with suitable connector