

# **EXCELSYS XSOLO**

ULTRA-COMPACT, HIGH-EFFICIENCY 500 W AND 1000 W SINGLE OUTPUT POWER SUPPLIES

Advanced Energy's Xsolo series, part of our Excelsys product line, delivers an incredible convection-cooled 504 W in an open-frame U-channel form factor and up to 1008 W in an enclosed, fan-cooled chassis. This high-efficiency, high-reliability product is available in two compact package types.



- Single output voltages are 24 V, 36 V, or 48 V with wide adjustment ranges and user-defined set-points
- Ultra high efficiency, > 92%
- Low profile: 1U height (40 mm)
- Convection-cooled 500 W
- Fan-cooled 1000 W (variable speed fan)
- 12 V/300 mA bias standby voltage provided
- Remote ON/OFF signal
- Power Good signal
- Suitable for type B-rated applications
- Optional PMBus<sup>™</sup> communications
- Optional OR-ing function
- Five-year warranty
- Adjustable output voltage control
- 5000 m altitude for EN60950 applications
- All models feature active power factor correction as standard
- Product options: Conformal coating, low leakage current and ruggedized

#### **TYPICAL APPLICATIONS**

- Industrial
- Test and measurement
- Acoustically sensitive laboratory and medical environments
- Hi-Rel MIL-COTS
- Communication

### AT A GLANCE

XS500	XS1000
Power	
504 W	1008 W
Output Voltage	
24, 36, 48	24, 36, 48

#### Certifications

- IEC60601-1 2nd and 3rd edition
- IEC60601-1-2 4th edition (EMC)
- IEC60950 2nd edition
- IEC62368-1
- 2 MOPP
- SEMI F47
- MIL-STD-810G<sup>2</sup>

# **MODELS**

Model	Power (W)	Output Voltage	Output Current (A)	Medical Approval UL/EN60601-1, 3rd Edition	Industrial Approval UL/EN60950, 2rd Edition
XS500-24	504	24	21.0	Yes	Yes
XS1000-24	1008	24	42.0	Yes	Yes
XS500-36	504	36	14.0	Yes	Yes
XS1000-36	1008	36	28.0	Yes	Yes
XS500-48	504	48	10.5	Yes	Yes
XS1000-48	1008	48	21.0	Yes	Yes

Model	Vnom (W)	Description	Set Point Adjust Range (V)	Dynamic Vtrim Range (V)	Imax (A)	Remote Sense	Power Good
XS500-24	24	Convection-cooled U-channel	19 to 28	14 to 28	21.0	Yes	Yes
XS1000-24	24	Enclosed fan-cooled	19 to 28	14 to 28	42.0	Yes	Yes
XS500-36	36	Convection-cooled U-channel	26 to 40	20 to 40	14.0	Yes	Yes
XS1000-36	36	Enclosed fan-cooled	26 to 40	20 to 40	28.0	Yes	Yes
XS500-48	48	Convection-cooled U-channel	36 to 58	29 to 58	10.5	-	Yes
XS1000-48	48	Enclosed fan-cooled	36 to 58	29 to 58	21.0	Yes	Yes

# **ELECTRICAL SPECIFICATIONS**

Input						
Parameter	Conditions/Decription		Min	Nom	Max	Units
Input Voltage Range	Universal input 47-440 Hz		85	_	264	VAC
	_		120	_	380	VDC
Power Rating	XS500		_	504	_	W
	XS1000		_	1008	_	W
Input Current	XS500		_	5	_	А
	XS1000		_	10	А	_
Inrush Current	230 VAC @ 25°C		_	_	25	А
Undervoltage Lockout	Shutdown		65	_	74	VAC
Fusing	XS500 250 VAC		_	F8A HRC	_	_
	XS1000 250 VAC		_	F12A HRC	_	_

Output						
Parameter	Conditions/Description	Min	Nom	Max	Units	
Output Voltage Range	XS500/1000-24: Multi-turn potentiometer	19	_	28	VDC	
	XS500/1000-24: Dynamic Vtrim range	14	_	28	VDC	
	XS500/1000-36: Multi-turn potentiometer	26	_	40	VDC	
	XS500/1000-36: Dynamic Vtrim range	20	_	40	VDC	
	XS500/1000-48: Multi-turn potentiometer	36	_	58	VDC	
	XS500/1000-48: Dynamic Vtrim range	29	_	58	VDC	



# ELECTRICAL SPECIFICATIONS (CONTINUED)

Output (Continued)					
Parameter	Conditions/Description	Min	Nom	Max	Units
Output Current Range	XS500-24	_	_	21	А
	XS1000-24	_	_	42	А
	XS500-36	_	_	14	А
	XS1000-36	_	_	28	А
	XS500-48	_	_	10.5	А
	XS1000-48	_	_	21	А
Load and Cross Regulation	For 25% to 75% load change	_	_	±0.2	%
	ORing option	_	_	±0.4	%
Transient Response	For 25% to 75% load change voltage deviation		_	2.5	%
	Settling time	_	_	500	μs
Ripple and Noise	XS500/1000-24: 20 MHz — 240m		240mV	_	pk-pk
	XS500/1000-36: 20 MHz		360 mV	_	pk-pk
	XS500/1000-48: 20 MHz	_	480 mV	_	pk-pk
Over-voltage Protection	XS500/1000-24: Latching	33	34	37	VDC
	XS500/1000-36: Latching	44	47	52	VDC
	XS500/1000-48: Latching	61	63	69	VDC
Over-current Protection	Straight line with hiccup activation at < 30% of Vnom.	105	115	130	%
Line Regulation	For ±10% change from nominal line	_	±0.5	_	%
Remote Sense	_	_	_	0.5	VDC
Overshoot	_	_	_	2	%
Rise Time	Monotonic		3	5	ms
Turn-On Delay	From AC in	_	500	800	ms
	From remote On/Off		10	_	ms
Hold-Up Time	For nominal output voltages at full load.	17	_	_	ms

General	General						
Parameter	Conditions/Description	Nom	Max	Units			
Isolation Voltage	Input to output	4000	_	_	VAC		
	Input to chassis	1500	_	_	VAC		
	Output to chassis	1500	_	_	VAC		
Efficiency	230 VAC, 1008 W @ 24 V/36 V/48 V	_	> 92	_	%		
Safety Agency Approvals	EN60601-1 2nd and 3rd Edition, cTUVus 60601-1	_	_	_	_		
	EN60950 2nd Edition, cTUVus 60950	_	-	_	_		
	EN62368 2nd Edition	_	_	_	_		
Leakage Current	akage Current 264 VAC, 60 Hz, 25°C		_	300	μΑ		
	264 VAC, 60 Hz, 25°C (Option 4)	_	_	150	μΑ		
Signals	See the designer's manual	_	_	_	_		
Bias Supply	Always on, current 300 mA XS1000, 50 mA XS500	_	12.0	_	VDC		
Weight XS500		_	1.1	_	Kg		
	XS1000		1.3		Kg		
MTBF	Telecordia SR-332, 40°C ground benign, parts count	_	_	550,000	Hours		



# **ELECTRICAL SPECIFICATIONS (CONTINUED)**


EMC	EMC					
Parameter	Standard	Level				
Emissions						
Conducted	EN55011, EN55022, FCC	Class B				
Radiated	EN55011, EN55022, FCC	Class B				
Harmonic Distortion	EN61000-3-2 Class A	Compliant				
Flicker and Fluctuation	EN61000-3-3	Compliant				
Immunity						
Electrostatic Discharge	EN61000-4-2	Level 2				
Radiated Immunity	EN61000-4-3	Level 3				
Fast Transients-Burst	EN61000-4-4	Level 3				
Input Line Surges	EN61000-4-5	Level 3				
Conducted Immunity	EN61000-4-6	Level 3				
Voltage Dips	EN61000-4-11, SEMI F47 compliant	Compliant				

Environmental							
Parameter	Conditions/Description	Min	Nom	Max	Units		
Operating Temperature	-40	_	+70	_	°C		
Storage Temperature	-40	_	+85	_	°C		
Derating	See the designer's manual for full temperature deratings	_	_	_	_		
Relative Humidity	Non-condensing 5 — 95		95	%RH			
Shock and Vibration	Designed to meet MIL810 G <sup>2</sup>	_	55	_	G		
Altitude	EN60601-1 Operational: 3000 m, Storage 8000 m	_	3000	_	m		
	EN60950 Operational: 5000 m, Storage 8000 m	_	5000	_	m		

# **Derating Curves**

The line voltage and temperatures derating curves for the XS500 and XS1000 are shown below. The XS500 is a 500 W convection-cooled part. The graphs below show the output power ratings with no system air flow and with 10 CFM of system air flow applied to the product.


Contact Advanced Energy for further information on the XS500 and XS1000 performance with system air flow applied to the product.



### **INTERFACE**

# **Input Connector J7**


Connector, Barrier Terminal Block, Vertical, 3 position, Pitch: 0.375 in Molex — 38720-7503



# O/P Connector J10 and J12

Connector, Barrier STRIP DL 3CIRC .325 Tyco — 2-1437667-5

\*Note: Maximum current per screw terminal is 20 Amps





# **Output Signal Connector J5**

Connector, Header 14POS 2MM Pitch T/H Molex — 87831-1420

# **J5 Mating Connectors**

Locking Molex 51110-1451; Non Locking 51110-1450; Crimp Terminal: Molex p/n 50394

# I<sup>2</sup>C Interface (Option)

The PMBus™ compatible interface can be used for monitoring the output voltage and current. It can also be used to manage real time data for the PSU. For full details on PMBus™ please contact Advanced Energy.


### **PMBus™ Connector**

PL1: Molex — 87833-0831

# **PL1 Mating Connector**

Locking Molex 51110-0860; Non Locking 51110-0850;

Crimp Terminal: Molex p/n 50394




Connector	Connector Details						
Pin	Input	Output	Signal	PMBus Connector			
1	L	+Vo	EN-	Not Used			
2	N	+Vo	EN+	GND			
3	PE	+Vo	PG+	Not Used			
4	_	-Vo	PG-	Not Used			
5	_	-Vo	12V	SCL			
6	_	-Vo	ACFail	Not Used			
7	_	_	OTP	Not Used			
8	_	_	Common	SDA			
9	_	_	Vtrim	_			
10	_	_	-Sns	_			
11	_	_	+Sns	_			
12	_	_	FanFail	_			
13	_	_	Itrim	_			
14	_	_	Common	_			

#### **XSOLO SERIES**

# **Paralleling Xsolo Products**

To achieve increased currents Xsolo products can be paralleled. To connect in parallel the outputs must be trimmed to within 5 mV of each other and then the current share header J20 must be added to each Xsolo product.


- Recommended Jumper for J20: HARWIN M7567-05
- (Jumper Socket, Black, 2.54 mm, 2-way)



#### **MECHANICAL SPECIFICATIONS**

## XS500-24

(All dimensions in mm)




# Mounting Holes

4 M3 threaded PEMS on Base, Max Screw Penetration is 6 mm from Base

### XS1000-24/XB1000-24

(All dimensions in mm)




# **Mounting Holes**

4 M3 threaded PEMS on Base, Max Screw Penetration is 6 mm from Base

#### NOTES

- 1 SEMI F47 compliant at input voltages > 160 VAC. Consult Advanced Energy for details.
- <sup>2</sup> Consult Advanced Energy for MIL810G report (enhanced ruggedisation available as an option).
- <sup>3</sup> System design with low leakage capacitors requires particular attention to EMI. Please consult Advanced Energy for application details.
- <sup>4</sup>Contact Advanced Energy for details including MOQs on alternative preset output voltages.
- <sup>5</sup>The specifications contained herein are believed to be correct at time of publication and are subject to change without notice.
- <sup>6</sup> All specifications at nominal input, full load, 25°C unless otherwise stated.
- <sup>7</sup>Compliance with MIL-STD-461 (CE101 & CE102) achieved with the addition of an external line filter from LCR p/n F19374.
- <sup>8</sup> Product is not UL/EN certified for 120-380 VDC input operation. Consult Advanced Energy for details.
- 9 Above 2000 m altitude, ambient operating temperature decreases by 1°C per 305 m (1000 ft) altitude increase

# CONFIGURATION



**Example 1:** XB1000-24N-000 = Xsolo 1000 W, 24 V, output with no options


**Example 2:** XB1000-24N-003 = Xsolo 1000 W, 24 V, output with PC/PMBus and OR-ing function

### **ABOUT ADVANCED ENERGY**

Advanced Energy (AE) has devoted more than three decades to perfecting power for its global customers. We design and manufacture highly engineered, precision power conversion, measurement and control solutions for mission-critical applications and processes.

Our products enable customer innovation in complex applications for a wide range of industries including semiconductor equipment, industrial, manufacturing, telecommunications, data center computing, and medical. With deep applications know-how and responsive service and support across the globe, we build collaborative partnerships to meet rapid technological developments, propel growth for our customers, and innovate the future of power.

PRECISION | POWER | PERFORMANCE





For international contact information, Advanced Energy® and AE® are U.S. trademarks, and CoolX® is a U.S. and visit advancedenergy.com

European trademark of Advanced Energy Industries, Inc.