

DATA SHEET

PTCP05 THERMISTOR NEEDLE PROBE

Needle Probes - 3.3 mm

Description

This probe uses the bulbous handle to enable the sensor tip to be pushed into a semi-solid product with maximum ease of use.

Construction

Needle Probe 3.3mm Diameter by 100mm Long : Stainless Steel 316 (Food Grade)
2M curly polyurethane cable to tails

Please note that this probe is not supplied with a connection plug for ease of hardwiring. Our thermistor probes can be purchased with jack plug as standard, other connection plugs available if required.
Jack plug order code: PTCPLUG

Sensor Features

➤ **TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.**

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

➤ **WATERPROOF HANDLE**

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

➤ **TOUGH POLYURETHANE CABLE**

- Polyurethane cables are used in place of the standard PVC for the following reasons :-
- Greater retractability
- Enhanced memory of it's curl
- Non-Toxic
- Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

➤ **HIGH ACCURACY THERMISTOR**

2k2 NTC Thermistor Sensor : (±0.2°C ±0.15%)

➤ **POLYPROPYLENE HANDLES**

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

- **WIDE AMBIENT TEMPERATURE SPECIFICATION** : -50 TO 50 °C
- **TIME RESPONSE (96% of value in water)** : 10 Secs
- **MEASUREMENT RANGE** : -50 TO 150 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

| TME PART No | DESCRIPTION | APPLICATION |
|-------------|-----------------------|--------------------------------------|
| MM2040 | THERMISTOR INSTRUMENT | HIGH ACCURACY THERMISTOR THERMOMETER |