

## Hinged-door cabinet with shelf and drawers

Doors with perforated panels

**RasterPlan**

### Application:

For clearly-arranged and space-saving storage of tools.

### Execution:

- Welded sheet steel structure with rear wall, ¼ slotted/¼ perforated panel for attaching support elements
- Overlay, double-walled, twist-resistant hinged doors, opening angle over 200°
- Three-point security cylinder lock with recessed turning handle



<b>Art. no.</b>	<b>50639 156</b>
<b>Brand</b>	RASTERPLAN
<b>Manufacturer Part Number</b>	1460.03.3024
<b>Door design</b>	Perforated boards
<b>Width</b>	1000 mm
<b>Depth</b>	600 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	2 PCS
<b>Shelf width</b>	1000 mm
<b>Shelf depth</b>	600 mm
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Number of drawers</b>	4 PCS
<b>Drawer front height</b>	4 x 100 mm
<b>With worktop</b>	No
<b>Load-carrying capacity per drawer</b>	110 kg
<b>Pullout type</b>	Full extension
<b>With partition wall</b>	No
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Lacquered
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Gross Weight</b>	137.000 kg
<b>Product Group</b>	5AC

### EAN

4251142237953