



GE
Lighting



PAR 64

SUPER CP60 EXC VNS 240V 1/6 BX

88551

Product information

PAR lamps provide a robust and flexible design solution for a wide range of applications. Choice of PAR36, PAR46, PAR56 or PAR64

- 3000 K or 4200 K colour temperature
- Choice of beam widths
- Excellent colour rendering
- High efficiency combined with low operating costs
- Robust and reliable
- UV control
- Easy retrofit
- Colour consistent throughout life
- Colour blends with halogen and fluorescent



Product data

EAN Code	0043168885515
DUN Code	10043168885512
Bulb Shape	PAR
Bulb Diameter [mm]	204
Cap/Base	GX16d
Nominal beam angle [°]	15
Dimming Capability	Yes
Gross weight per piece [g]	1072
Maximum Overall Length [mm]	150
Net weight per piece [g]	965
Brand	General Electric (GE)

Performance data

Nominal power [W]	1000
Nominal lamp voltage [V]	240
Nominal correlated colour temperature (CCT) [K]	3200
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	300
Ballast Required	No
Nominal center beam candlepower (CBCP) [cd]	352000
Coil type	C-13D
Energy efficiency class (EEC)	C
Weighted energy consumption [kWh/1000h]	1036.2

Logistic data

Pack Quantity	6
Pallet quantity EUR (PC)	120
Pallet quantity UK (PC)	150
Outer case size	536 x 391 x 196 (mm)
Layer quantity	24 EUR, 30 UK
Layer quantity EUR	24
Layer quantity UK	30
Product status	Available

Application areas



Club and Disco

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Special purpose lamp – Stage Studio. Not suitable for household illumination.