

PRODUCT-DETAILS

# OVR T2 1N 40-275 P QS

## OVR T2 1N 40-275 P QS Surge Protective Device



### General Information

Extended Product Type	OVR T2 1N 40-275 P QS
Product ID	2CTB803972R1100
EAN	3660308519696
Catalog Description	OVR T2 1N 40-275 P QS Surge Protective Device
Long Description	Surge protective devices SPD type 2 protect low-voltage consumer systems against surge voltages as they are tested as SPD type 2 according to IEC 61643-11. The devices are compatible with the System pro M compact series. The SPD with "TS" are optionally equipped with a auxiliary contact.

### Technical

Standards	IEC 61643-11 / EN 61643-11
Type of Low Voltage Distribution System	TT TN-S
Suitable For	To protect the systems against the transient overvoltage (lightning)
Rated Voltage ( $U_r$ )	230 V AC
Nominal AC Voltage of the System ( $U_o$ )	230 / 400 V
Voltage Rating DC	350 V
Voltage Protection Level ( $U_p$ )	1.5 kV (L-N) 1.25 kV (N-PE) 1.4 kV

Maximum Continuous Operating Voltage ( $U_c$ )	(L-PE) 275 V (L-L) - V (L-N) 275 V (N-PE) 275 V
Temporary Overvoltage Test Value ( $U_T$ )	(L-N) 337 V (N-PE) 1200 V
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	100 kA
Discharge Current	Nominal 20 kA Maximum 40 kA Total 80 kA Nominal (8 / 20 $\mu$ s) 20 kA I (max, 8 / 20 $\mu$ s) 80 kA
Impulse Current	I (imp, 10 / 350 $\mu$ s) 2 kA
Short Circuit Withstand $I_{cc}$	100 kA
Power Loss	17 mW
Short-Circuit Protective Devices	Curve B Breakers $\leq$ 125 A Curve C Breakers $\leq$ 125 A gL Type Fuses $\leq$ 125 A gG Type Fuses $\leq$ 125 A
Arrester Class	II
Number of Poles	2
Number of Protected Poles	2
Number of Conductors	2
Position of Neutral Terminals	Right
Transmission Standard	Optic
Version	Plug-in
Mounting Type	DIN rail (top hat rail) 35 mm
Product Type	QS
Options Provided	Residential, commercial building.
Auxiliary Circuit Load	Minimum - Maximum -
Preventive Maintenance Feature	No
Status Indicator	Yes
Fuse Size	2 modular spacing

## Environmental

Degree of Protection	IP20
Maximum Operating Altitude Permissible	Without Derating 5000

## Dimensions

Width in Number of Modular Spacings	2
Product Net Width	35.6 mm
Product Net Height	88 mm
Product Net Depth / Length	58 mm

Product Net Weight	0.24 kg
--------------------	---------

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	117 mm
Package Level 1 Height	82 mm
Package Level 1 Depth / Length	41 mm
Package Level 1 Gross Weight	250 g
Package Level 1 EAN	3660308519696

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country of Origin	Bulgaria (BG)

## Certificates and Declarations (Document Number)

CB Certificate	2CTC432024G1701
CQC Certificate	9AKK107680A1974
Declaration	2CTC432056G1701
Declaration of Conformity - CE	9AKK108466A4410
Instructions and Manuals	2CTC432096M1701

## Popular Downloads

Data Sheet, Technical Information	2CTC432219D0201
Instructions and Manuals	2CTC432096M1701
Mechanical Drawings	2CTC800021F1100.pdf 2CTC800021F1101.dxf 2CTC800021F1102.stp 2CTC800021F1103.igs

## Classifications

ETIM 7	EC000941 - Surge protection device for power supply systems
ETIM 8	EC000941 - Surge protection device for power supply systems
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363090
Object Classification Code	141DCC

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Surge Protective Devices SPDs → Surge Protective Devices SPD Class II → Type T2 40kA

