



Dimensions: [mm]












Product Marking:

| Start of Winding | • |
|------------------|-----------------------|
| Marking | 6R8 (Inductance Code) |

Recommended Land Pattern: [mm]




no vias and sensitive traces underneath the component

Scale - 4:1

The width dimension of the soldering terminal is specified without

Schematic:



Electrical Properties:

| Properties | | Test conditions | Value | Unit | Tol. |
|------------------------------|----------------------|-----------------|-------|------|------|
| Inductance | L | 100 kHz/ 10 mA | 6.8 | μН | ±20% |
| Rated Current | I _{R,40K} | ΔT = 40 K | 6.5 | А | max. |
| Performance Rated Current 1) | I _{RP,40K} | ΔT = 40 K | 8.1 | А | max. |
| Saturation Current @ 10% | I _{SAT,10%} | IΔL/LI < 10 % | 5.65 | А | typ. |
| Saturation Current @ 30% | I _{SAT,30%} | IΔL/LI < 30 % | 11.3 | А | typ. |
| DC Resistance | R _{DC} | @ 20 °C | 17.6 | mΩ | ±10% |
| Self Resonant Frequency | f _{res} | | 22 | MHz | typ. |

¹⁾ refer to IEC 62024-2-2020

Certification:

| RoHS Approval | Compliant [2011/65/EU&2015/863] |
|-------------------------|-------------------------------------|
| REACh Approval | Conform or declared [(EC)1907/2006] |
| Halogen Free | Conform [JEDEC JS709B] |
| Halogen Free | Conform [IEC 61249-2-21] |
| Component Qualification | AEC-Q200 Grade 1 |
| Automotive Approval | Released |

General Information:

CHECKED

REVISION

DATE (YYYY-MM-DD)

| Ambient Temperature (referring to $I_{\rm R}$) | -40 up to +85 °C |
|---|--------------------|
| Operating Temperature | -40 up to +125 °C |
| Storage Conditions (in original packaging) | < 40 °C; < 75 % RH |
| Moisture Sensitivity Level (MSL) | 1 |

Test conditions of Performance Rated Current: refer to IEC 62024-2, Class D (PCB Copper Width: 40 mm; PCB Copper Thickness: 1000 μm)

Temperature rise is highly dependent on many factors including PCB land pattern, trace size, and proximity to other components. Therefore, temperature rise should be verified in application conditions.

GENERAL TOLERANCE





Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

PROJECTION METHOD WE 001.002 2030-01-01 DIN ISO 2768-1m **WE-XHMA SMT Power Inductor** ORDER CODE 78439346068 SIZE/TYPE BUSINESS UNIT STATUS PAGE 6060 Valid 1/8 eiSos

Typical Inductance vs. Current Characteristics: Typical Temperature Rise vs. Current Characteristics: 100 8 -IR **IRP** 90 7 80 6 70 Temperature Rise [K] Inductance [µH] 50 3 30 2 20 10 0 0 2 6 8 10 12 6 12 10 Current [A] Current [A] CHECKED DATE (YYYY-MM-DD) GENERAL TOLERANCE REVISION WE 001.002 2030-01-01 DIN ISO 2768-1m HALOGEN **WE-XHMA SMT Power Inductor** Würth Elektronik eiSos GmbH & Co. KG ORDER CODE EMC & Inductive Solutions WURTH ELEKTRONIK Max-Eyth-Str. 1 78439346068 74638 Waldenburg

MORE THAN YOU EXPECT

Germany

Tel. +49 (0) 79 42 945 - 0

www.we-online.com

eiSos@we-online.com

SIZE/TYPE

6060

STATUS


Valid

PAGE


2/8


BUSINESS UNIT


eiSos



Packaging Specification - Tape: [mm]










| Таре Туре | A0 (mm) | B0 (mm) | W (mm) | T (mm) | T1 (mm) | T2 (mm) | K0 (mm) | P0 (mm) | P1 (mm) | P2 (mm) | D0 (mm) | D1 (mm) | E1 (mm) | E2 (mm) | F (mm) | Material | Qty. (pcs.) |
|-----------|------------|------------|------------|-----------|------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|-------------|----------------|
| | typ. | typ. | +0,3/ -0,1 | ref. | max. | typ. | typ. | ±0,1 | ±0,1 | ±0,1 | +0,1/-0,0 | min. | ±0,1 | min. | ±0,1 | | |
| 2a | 7.00 | 6.80 | 16.00 | 0.40 | 0.10 | 6.50 | 6.40 | 4.00 | 12.00 | 2.00 | 1.50 | 1.50 | 1.75 | 14,25 | 7.50 | Polystyrene | 700 |

Packaging Specification - Reel: [mm]





| | A (mm) | B (mm) | C (mm) | D (mm) | N (mm) | W1 (mm) | W2 (mm) | W3 (mm) | W3 (mm) | Material |
|-----------|-----------|-----------|-----------|-----------|-----------|------------|------------|------------|------------|-------------|
| Tolerance | ± 2,0 | min. | min. | min. | min. | + 2,0 | max. | min. | max. | |
| Value | 330,00 | 1,50 | 12,80 | 20,20 | 60,00 | 16,40 | 22,40 | 15,90 | 19,40 | Polystyrene |



Pull-of force Tape width 16 mm 0,1 N - 1,3 N





Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg

WE


Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

CHECKED GENERAL TOLERANCE PROJECTION METHOD REVISION DATE (YYYY-MM-DD) 001.002 2030-01-01 DIN ISO 2768-1m

WE-XHMA SMT Power Inductor ORDER CODE


78439346068 SIZE/TYPE BUSINESS UNIT STATUS PAGE 6060 eiSos Valid 4/8

Packaging Specification - Reel in Carton: [mm]




| L _{IC} (mm) | W _{IC} (mm) | H _{IC} (mm) | No. of Reel (pcs.) | Qty. (pcs.) | Material |
|----------------------|----------------------|----------------------|-----------------------|----------------|----------|
| typ. | typ. | typ. | | | |
| 0.40.00 | 0.40.00 | 05.00 | 0 | 0400 | 5 |


Packaging Specification - Outer Carton: [mm]



| | L _C (mm) | W _C (mm) | | No. of Inner Carton (pcs.) | Qty. (pcs.) | Material |
|----|------------------------|------------------------|--------|-------------------------------|----------------|----------|
| -[| typ. | typ. | typ. | | | |
| ı | 355,00 | 355,00 | 385,00 | 3 | 6300 | Paper |



Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

| Profile Feature | | Value | | | | | |
|--|--------------------|---------------------------------|--|--|--|--|--|
| Preheat Temperature Min T_s | | 150 °C | | | | | |
| Preheat Temperature Max | T _{s max} | 200 °C | | | | | |
| Preheat Time t_s from $T_{s min}$ to $T_{s max}$ t_s | | 60 - 120 seconds | | | | | |
| Ramp-up Rate (T _L to T _P) | | 3 °C/ second max. | | | | | |
| Liquidous Temperature | T _L | 217 °C | | | | | |
| Time t_L maintained above T_L | t _L | 60 - 150 seconds | | | | | |
| Peak package body temperature | T _p | $T_p \le T_c$, see Table below | | | | | |
| Time within 5°C of actual peak temperature | t p | 20 - 30 seconds | | | | | |
| Ramp-down Rate (T _P to T _L) | | 6 °C/ second max. | | | | | |
| Time 25°C to peak temperature | | 8 minutes max. | | | | | |

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature (T_c):

| Properties | Volume mm³ <350 | Volume mm ³ 350-2000 | Volume mm³ >2000 |
|---|--------------------|------------------------------------|------------------|
| PB-Free Assembly Package Thickness < 1.6 mm | 260 °C | 260 °C | 260 °C |
| PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm | 260 °C | 250 °C | 245 °C |
| PB-Free Assembly Package Thickness > 2.5 mm | 250 °C | 245 °C | 245 °C |

refer to IPC/ JEDEC J-STD-020E

| | ROHS REACH HALOGEN 125 CC COMPLIANT COMPLIANT FREE GRADE 1 | | WE | 001.002 | DATE (YYYY-MM-DD) 2030-01-01 | DIN ISO 2768-1m | | PROJECTION METHOD | ⊕- |
|--|--|---|-------------------|---------|---------------------------------|------------------------|-----------------|-------------------|-------------|
| ROHS REACH HALOC COMPLIANT COMPLIANT FREE | | | DESCRIPTION WE-XI | HMA SN | IT Power li | | | | |
| L//E ELE | WURTH ELEKTRONIK MORE THAN YOU EXPECT | Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany | | | | | 784 | 39346068 | |
| MOF | | Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com | SIZE/TYPE 6060 | | | BUSINESS UNIT eiSos | status Valid | | PAGE 6/8 |

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-XHMA of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the
 authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the part, resulting in a void of the warranty.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
 insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
 degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
 shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.
- Due to heavy weight of the components, strong forces and high accelerations might have the effect to damage the electrical connection
 or to harm the circuit board and will void the warranty.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

