

Rubber-Flex collets

Accessories for Tapmatic thread cutting apparatus



Application:

For drill bits and screw taps with straight shank (Tapmatic thread cutters).

Execution:


- Clamping segments are securely attached with special rubber.
- Clamping segments move in parallel along the complete clamping range.
- High radial clamping force
- Tool shank is clamped along the entire length of the hole.

Advantage:

- Centric and precise clamping within the entire clamping range.
- Concentricity properties remain constant even with tolerance clamping.
- Concentricity properties remain constant even with tolerance clamping

Delivery:

1x Rubber Flex collet chuck.



Art. no.	21655 070
Brand	ORTLIEB
Manufacturer Part Number	RFCJ422
Collet type	J 422
Min./max. clamping range	6.5-10 mm
Gross Weight	0.001 kg
Product Group	241

