

Heavy-duty cabinet with central partition

With solid sheet metal doors, with drawers and shelves

RasterPlan

Application:

For a total loading capacity of up to 1.65 t for very heavy loads, particularly suitable for storage of the heaviest tools, such as embossing and punching dies.

Execution:

- Extremely stable welded steel structure with brazed corners, with central partition
- Smooth fronts due to flush overlay doors, opening angle more than 200°, continuous rod guiding
- Doors can be locked simultaneously with a triple-point security cylinder lock, incl. 2 keys
- Cabinet base can carry a load of up to 400 kg

Delivery:

Additional door designs (for 1950 mm height), e.g. perforated or slotted panel doors and sidewall lining, drawer locks and suitable insert materials with compartment dividers, additional group keys or main keys and further paint colours deliverable on request.



Art. no.	50047 232
Brand	RASTERPLAN
Manufacturer Part Number	1472.03.2016
Door design	Full-sheet panel
Width	1000 mm
Depth	600 mm
Height	1110 mm
Load-carrying capacity per shelf	80 kg
Number of drawers	16 PCS
Drawer front height	16 x 125 mm
Drawer width (inner dimension)	889 mm
Drawer depth (inner dimension)	483 mm
Load-carrying capacity per drawer	110 kg
Pullout type	Full extension
With partition wall	Yes
Load-carrying capacity	1650 kg
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Cabinet colour	Light grey RAL 7035
Gross Weight	193.000 kg
Product Group	5AC

EAN

4251142219188