



Part Number : [1300350057](#)

Product Description : DeviceNet 5 Pole, Tee  
Female to Male

Series Number : 130035

Status : Active

Product Category : Industrial Tees and  
Splitters

Engineering Number : DN3020



---

## Documents & Resources


### Drawings

[Drawing 1300350057\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT\_UKCA - Declaration of Conformity : CER\_4000410285\_00\_000.pdf

ZZCERT\_CE - Declaration of Conformity : CER\_4000408918\_00\_000.pdf

---

## Part Details

### General

Status	Active
Category	Industrial Tees and Splitters
Series	130035
Description	DeviceNet 5 Pole, Tee Female to Male
IP Rating	IP67
Product Family	DeviceNet Solutions
Product Name	DeviceNet Trunk
Type	Drop Tee
UPC	78172553130

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

### Physical

Color - Cable Jacket	Gray
Drop Connector	Mini-Change
Drop Gender	Female
Keyway	Single
LED Indicator	No
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female

Leg 1 Length	N/A
Leg 2 Length	N/A
Length	0.072m
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Die-Cast Zinc
Net Weight	95.254/g
Poles	5
Right Trunk Connector	Mini-Change
Right Trunk Gender	Male
Temperature Range - Operating	-20°C to +80°C

---

This document was generated on Sep 27, 2023