

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



tasker® C701 S.-F.T.P. Cat. 5e 4x2x0,14mm² - UL/ETL verified Cable



ETHERSOUND CATEGORY

Stranded conductors EIA/TIA 568-suitable not only for RJ 45 8 Pin.
 High Frequency Transmission Data (See Audio Catalogue).

- A:** Blue-Night **PVC** sheath - Outer Dim. Ø 7,00 (±0,20) mm.
- B:** First Shielding with a Braid of O.F.C. tinned copper covering 70% + Drain Wire.
- C:** Second shielding with Aluminum tape, covering 100%.
- D:** The four pairs are stranded together with polyester based tape.
- E:** Insulation with PE – Diam. Ø 0,90 mm - RJ45 plug connector compatible.
 Core colors: white-blue/Blue, white-Orange/Orange, white-green/Green, white-brown/Brown.
- F:** Stranded formation of 7x0,15 mm in O.F.C. Red Copper.
 Nom. Cross section 4x2x0,14mm².

MARKING

tasker® C701 E-TYPE CM 26 AWG 60°C (UL) E188630 CSA LL81295 FT4 ETL Verified ITA/EIA-568-B.2 Cat.5e PATCH CABLE S.-F.T.P.

CUSTOM

This product is also available in **L.S.Z.H.** polymer, **PE**, **PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	140 Ω/Km ± 5%
Impedance	100 Ω± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	INSTALLATION	<input checked="" type="checkbox"/>	Fixed	Fissa	INFORMATION	<input checked="" type="checkbox"/>	RoHS2 Compliant
Impiego	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	Posa	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	Informazioni	<input checked="" type="checkbox"/>	Ver C / 30.06.16
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		