

IQ40-20BPPKCOK

INDUCTIVE PROXIMITY SENSORS





Ordering information

| Туре | Part no. |
|----------------|----------|
| IQ40-20BPPKC0K | 1071553 |

Included in delivery: BEF-KH-IQ40 (1)

Other models and accessories → www.sick.com/IQG







Detailed technical data

Features

| Housing | Rectangular |
|-----------------------------------|----------------------------------|
| Housing | Short-body |
| Dimensions (W x H x D) | 40 mm x 40 mm x 66 mm |
| Sensing range S _n | 20 mm |
| Safe sensing range S _a | 16.2 mm |
| Installation type | Flush |
| Switching frequency | 150 Hz |
| Connection type | Male connector M12, 4-pin |
| Switching output | PNP |
| Output function | Complementary |
| Electrical wiring | DC 4-wire |
| Enclosure rating | IP67, IP68, IP69K |
| Special applications | Difficult application conditions |

Mechanics/electronics

| Supply voltage | 10 V DC 30 V DC |
|--|------------------------------------|
| Ripple | ≤ 10 V _{pp} ¹⁾ |
| Voltage drop | ≤ 2 V |
| Time delay before availability | ≤ 50 ms |
| Hysteresis | 3 % 15 % ²⁾ |
| Reproducibility | ≤ 2 % |
| Temperature drift (of S _r) | ± 10 % |
| Continuous current I _a | ≤ 200 mA |
| Short-circuit protection | ✓ |
| Reverse polarity protection | ✓ |

¹⁾ Of Ub.

 $^{^{2)}}$ Of S_{r} .

³⁾ Reference voltage: 50 V DC.

| Power-up pulse protection | ✓ |
|--------------------------------|--------------------------------|
| Shock and vibration resistance | 30 g, 11 ms / 10 55 Hz, 1 mm |
| Ambient operating temperature | -25 °C +85 °C |
| Ambient temperature, storage | -40 °C +85 °C |
| Housing material | Plastic, PA 66 |
| Sensing face material | Plastic, PA 66 |
| Tightening torque, max. | 1.8 Nm |
| Items supplied | Push-lock mounting system (1x) |
| Protection class | II ³⁾ |
| UL File No. | E348498 |

¹⁾ Of Ub.

Safety-related parameters

| MTTF _D | 1,406 years |
|-------------------|-------------|
| DC _{avg} | 0 % |

Reduction factors

| Note | The values are reference values which may vary | |
|----------------------------|--|--|
| Stainless steel (V2A, 304) | Approx. 0.71 | |
| Aluminum (AI) | Approx. 0.3 | |
| Copper (Cu) | Approx. 0.25 | |
| Brass (Br) | Approx. 0.36 | |

Installation note

| Remark | Associated graphic see "Installation" |
|--------|---------------------------------------|
| Α | 0 mm |
| В | 40 mm |
| c | 40 mm |
| D | 60 mm |
| E | 0 mm |
| F | 70 mm |

Classifications

| ECI@ss 5.0 | 27270101 |
|--------------|----------|
| ECI@ss 5.1.4 | 27270101 |
| ECI@ss 6.0 | 27270101 |
| ECI@ss 6.2 | 27270101 |
| ECI@ss 7.0 | 27270101 |
| ECI@ss 8.0 | 27270101 |
| ECI@ss 8.1 | 27270101 |
| ECI@ss 9.0 | 27270101 |
| ECI@ss 10.0 | 27270101 |
| ECI@ss 11.0 | 27270101 |

²⁾ Of S_r.


³⁾ Reference voltage: 50 V DC.

IQ40-20BPPKC0K | IQG

INDUCTIVE PROXIMITY SENSORS

| ETIM 5.0 | EC002714 |
|----------------|----------|
| ETIM 6.0 | EC002714 |
| ETIM 7.0 | EC002714 |
| ETIM 8.0 | EC002714 |
| UNSPSC 16.0901 | 39122230 |

Installation note




Connection diagram

Cd-009

Characteristic curve


IQ40-20Bxxxxx





Dimensional drawing (Dimensions in mm (inch))

IQG Short-body housing



- ① LED output state, yellow
- ② Sensing face③ Operational status LED, green

Recommended accessories

Other models and accessories → www.sick.com/IQG

| | Brief description | Туре | Part no. |
|----------------------------|---|------------------------|----------|
| Plug connectors and cables | | | |
| | Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m | YF2A14- 050VB3XLEAX | 2096235 |
| 3 | Head A: female connector, M12, 4-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m | YG2A14- 050VB3XLEAX | 2095897 |
| | Head A: female connector, M12, 4-pin, straight Head B: - Cable: unshielded | DOS-1204-G | 6007302 |
| W/S | Head A: male connector, M12, 4-pin, straight Head B: - Cable: unshielded | STE-1204-G | 6009932 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

