


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/17/11	D.GRIFFIN



(2X) 20 PIN DISPLAYPORT MALE CONNECTOR

WIRING MAP				
CABLE	"P1"	SIGNAL NAME	COLOR	"P2"
TWISTED PAIR 1	1	ML_LANE 0(p)	BROWN	12
	2	GND	DRAIN	11
	3	ML_LANE 0(n)	WHITE	10
TWISTED PAIR 2	4	ML_LANE 1(p)	RED	9
	5	GND	DRAIN	8
TWISTED PAIR 3	6	ML_LANE 1(n)	WHITE	7
	7	ML_LANE 2(p)	GREEN	6
TWISTED PAIR 4	8	GND	DRAIN	5
	9	ML_LANE 2(n)	WHITE	4
TWISTED PAIR 5	10	ML_LANE 3(p)	ORANGE	3
	11	GND	DRAIN	2
	12	ML_LANE 3(n)	WHITE	1
	13	GND	BROWN	13
	14	GND	RED	14
TWISTED PAIR 5	15	AUX CH(p)	BLUE	15
	16	GND	DRAIN	16
	17	AUX CH(n)	WHITE	17
	18	HOT PLUG DETECT	YELLOW	18
	19	DP_PWR RETURN	ORANGE	19
	20	N/A	N/C	20
	SHELL	GND	BRAID	SHELL

PART NUMBER	LENGTH	
	METERS	FEET
DPCAMM-0.5	0.5	1.64
DPCAMM-1	1.0	3.28
DPCAMM-2	2.0	6.56
DPCAMM-3	3.0	9.84
DPCAMM-4	4.0	13.12
DPCAMM-5	5.0	16.41
DPCAMM-10	10.0	32.81
DPCAMM-15	15.0	49.22

**RoHS Compliant** ✓

- NOTES:  
 1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.  
 2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	01/14/2011		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. CASTRO	01/14/2011	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY P. McNEIL	01/14/2011	DISPLAYPORT CABLE M/M	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. DPCAMM-X	REV. <b>A</b>
			SCALE: NONE	CAD FILE: DPCAMM-X.SLDDRW
				SHEET 1 OF 1