



**Incomer module, 3 pole, 1.5-16qmm, 80 A**

**Part no. MSFI-80A**  
**Catalog No. 191093**  
**Eaton Catalog No. MSFI-80A**


**Delivery program**

Product range			Accessories
Accessories			feeder module
Material			Halogen free
Self-extinguishing			to UL 94
Track resistance			CTI 600
Temperature resistant			to 125 °C
Connection technique			Spring-loaded terminals
Width		mm	23
Pole			3
Rated operational current	$I_e$	A	80
<b>Terminal capacity</b>			
conductor			1.5 - 16 mm <sup>2</sup> AWG 14 - 6
For use with			MSFB...

**Technical data ETIM 6.0**

Low-voltage industrial components (EG000017) / Busbar terminal (EC000001)			
Electric engineering, automation, process control engineering / Electrical installation, device / Clamp (not overhead line) / Switch board (ec1@ss8.1-27-14-11-46 [BAA025010])			
Busbar thickness		mm	0 - 0
Busbar width		mm	0 - 0
Suitable for			-
Width clamp		mm	23
Max. conductor cross section		mm <sup>2</sup>	16
Max. rated operation current $I_e$		A	80
Suitable for round conductor connection			Yes
Suitable for sector conductor connection			No
Suitable for strip conductor connection			No

## Dimensions



## Additional product information (links)

### IL015081ZU Incomer module

IL015081ZU Incomer module [ftp://ftp.moeller.net/DOCUMENTATION/AWA\\_INSTRUCTIONS/IL015081ZU2017\\_04.pdf](ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL015081ZU2017_04.pdf)

Motor starters and "Special Purpose Ratings" for the North American market [http://www.moeller.net/binary/ver\\_techpapers/ver953en.pdf](http://www.moeller.net/binary/ver_techpapers/ver953en.pdf)

Busbar Component Adapters for modern Industrial control panels [http://www.moeller.net/binary/ver\\_techpapers/ver960en.pdf](http://www.moeller.net/binary/ver_techpapers/ver960en.pdf)