### Characteristics

	IP67			
Rating	IEC 60947-5-1	AC-15 240V AC / 3A, DC-13 250V DC / 0.27A		
-	UL508	A300 250V AC / 15A		
	Mechanical	1,000,000 operations min.		
Durability	Electrical	500,000 operations min. (3A resistive load at 250VC) 300,000 operations min. (10A resistive load at 250V AC)		
	0.05 to 0.5m/s			
Operating Frequency	Mechanical	- 30 operations/minute max.		
	Electrical			
	50/60Hz			
	100MΩ min.			
	25mΩ max.			
	Between terminals of same polarity	2.5kV		
Dielectric Strength	Between current-carrying metal parts and ground	4kV		
	Between each terminal and non-current-carrying metal part	6kV		
	300V			
Р	3 (EN60947-5-1)			
	100A (EN60947-5-1)			
(	10A (EN60947-5-1)			
D	Class II			
Vibration Resistance	Malfunction	10~55 Hz 0.75mm single amplitude		
Oh a als Da aistar	Destruction	1,000m/s² min.		
Shock Resistance	Malfunction	300m/s <sup>2</sup> min.		
	-30°C ~ +70°C with no icing			
Ambient operating humidity range 95% Max.				

Notes:

1. Above values of these characteristics are initial values.

2. Above values of these characteristics may are depending on different models.

3. Above durability is for an ambient temperature of 5 to 35° and ambient humidity of 40% to 70%.


### **Operating Characteristics**

Part Number	Key Insertion Force	Key Extraction Force	Pre Travel (Max.)	Total Travel	Direct Opening Force	Direct Opening Stroke
MC002456	15N	30N	6 ±3mm	28mm	60N	10mm
MC002458	15N	30N	6 ±3mm	28mm	60N	10mm
MC002459						

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




### With Front-inserted Operation Key



Weight: 120.6g


# With Adjustable Front-inserted Operation Key in Horizontal Mount



Weight: 108.8g

-21.50

## With Adjustable Front-inserted Operation Key in Horizontal and Vertical Mount



MC002459 Weight: 116.1g

**Dimensions : Millimetres** 

#### Part Number Table

Description		
Vertical Limit Switch, Miniature Safety, w/ Front-Inserted Operation Key, Screw Terminal	MC002456	
Vertical Limit Switch, Miniature Safety, w/ Adjustable Front-Inserted Operation Key in Horizontal Mount, Screw Terminal	MC002458	
Vertical Limit Switch, Miniature Safety, w/ Adjustable Front-Inserted Operation Key in Horizontal and Vertical Mount, Screw Terminal	MC002459	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

