

Twist drill type N HSS

For universal use up to 1000 N/mm²

ATORN[®]



Application

Standard geometry for universal use up to 1000 N/mm².

Version

- Twist drill with universal standard geometry

Advantage

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Vaporisation ensures favourable adherence of coolant

| Application | Steel (N/mm ²) | | | Stainless steel | | Alu | | Brass | | Bronze | | Plas-tics | Graphite G(C)FK | GG(G) GJMW | Titan-alloy | Nickel-alloy | Super-alloy | Hard mat. | |
|-------------|----------------------------|-------|-------|-----------------|---------|-------|------|-------|------|--------|------|-----------|-----------------|------------|-------------|--------------|-------------|-----------|---------|
| | <700 | <1000 | <1300 | marten. | austen. | short | long | short | long | short | long | | | | | | | <55 HRC | <65 HRC |
| | 20 | 10 | | | | 40 | 50 | 40 | 30 | 30 | 20 | 10 | | 20 | | | | | |

| | |
|------------------------------|-------------------|
| Art. No. | 11063 360 |
| Cutting material | HSS |
| Surface | Vaporised |
| Type | N |
| Angle of the tip | 118 Degree |
| Tool holding device | HA parallel shank |
| Cutting edge diameter | 12.00 mm |
| Chip flute length | 200 mm |
| Length | 250 mm |
| f steel 700 | 0.24 mm/U |
| DIN | 1869 |

EAN-Code

4050293033311