

## RKE high-pressure machine vices

Mechanical-hydraulic clamping system



### Application:

For NC machines, machining centres in tool manufacture, mould making jog manufacturing and serial production.

### Execution:

- Ref. no. 092 horizontal insert, mechanical-hydraulic clamping system with hand crank.
- Robust steel basic body.
- All guides are hardened and polished on all sides.
- Central grease nipple for simple lubrication of guides and spindle thread.
- Polished functional surfaces.
- Drive spindle with preset clamping force via stop.
- Clamping surface for adjustable clamps.
- Clamping repeatability with identical clamping force: 0.01 mm.
- Can be clamped horizontally, laterally and (with a base plate) vertically.

### Advantage:

- Optimised design for better chip removal.
- Reliable chip protection prevents swarf penetrating inside the body.

### Delivery:

1x RKE high-pressure machine vice with 1 set of stepped jaws and 1x hand crank



<b>Art. no.</b>	<b>28878 092</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	178411
<b>Jaws width</b>	92 mm
<b>Jaws height</b>	32 mm
<b>Body length</b>	276 mm
<b>Max. length</b>	346 mm
<b>Min./max. clamping width</b>	71-138 mm
<b>Tension force</b>	25 kN
<b>Weight</b>	15 kg
<b>Travel stroke of gate valve</b>	70 mm
<b>Offset range 2</b>	1 x 68 mm
<b>Gross Weight</b>	16.750 kg
<b>Product Group</b>	284

### EAN

4019208244709