

# **DATA SHEET**

## **METAL FILM RESISTORS**

Precision MFP Series

1/6W to 3W RoHS compliant & Halogen Free



**YAGEO** 





**APPLICATIONS** 

High precision circuit

Measurement instruments

Power applications

Medical equipment

Industrial electronic

AEC-Q200 qualified

Wide resistance range

Narrow tolerance & low TCR

**FEATURES** 

High stability

RoHS compliant & halogen-free

#### **ORDERING INFORMATION**

Part number of the precision metal film resistors are identified by the series, power rating, tolerance, packing, temperature coefficient, forming and resistance value.

### **PART NUMBER**

<b>MFP</b>	<u>200</u>	<u>B</u>	<u>T</u>	<u>D</u>	<u>73-</u>	<u>100R</u>
(1)	(2)	(3)	(4)	(5)	(6)	(7)

#### (1) SERIES

MFP Series

#### (2) POWER RATING

-12 = 1/6W -50 =	1/2W
25S = 1/4W 1WS =	= 1W
204=0.4W 100 =	1W
-25 = 1/4W 2WS =	= 2W
50S = 1/2W 200 =	2W
207=0.6W 3WS =	= 3W

#### (3) TOLERANCE

$B = \pm 0.1\%$	$A = \pm 0.05\%$
C = +0.25%	P- +0.02%

#### (4) PACKAGING

R = Reel Pack	B = Bulk
T = Box Pack	

#### (5) TEMPERATURE COEFFICIENT OF RESISTANCE

$A = \pm 5$ ppm/°C	$C = \pm 15 ppm/^{\circ}C$
$B = \pm 10 ppm/^{\circ}C$	$D = \pm 25 ppm/^{\circ}C$

#### (6) FORMING

Note: 26mm, 52.4mm and 73mm represent dimension A of the axial type, please refer to the category of AXIAL/REEL TAPE SPECIFICATION for the detail.

#### (7) RESISTANCE VALUE


E192 Series Example:

 $100R = 100\Omega$ ,  $10K = 10,000\Omega$ ,  $1M = 1,000,000\Omega$ 

### **DIMENSIONS**

For ±0.1% tolerance


Unit: mm



Normal	Miniature	L	ψD	Н	ψd
MFP-12	MFP25S	$3.4 \pm 0.3$	1.9 ± 0.2	28 ± 2.0	0.56 ± 0.05
MFP204	-	$3.4 \pm 0.3$	1.9 ± 0.2	28 ± 2.0	0.56 ± 0.05
MFP-25	MFP50S	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	$0.65 \pm 0.05$
MFP207	-	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	$0.65 \pm 0.05$
MFP-50	MFP1WS	9.0 ± 0.5	$3.3 \pm 0.3$	26 ± 2.0	0.65 ± 0.05
MFP100	MFP2WS	11.5 ± 1.0	$4.5 \pm 0.5$	35 ± 2.0	$0.8 \pm 0.05$
MFP200	MFP3WS	15.5 ± 1.0	$5.0 \pm 0.5$	33 ± 2.0	0.8 ± 0.05


For ±0.25%,±0.02%,±0.05% tolerances

Unit: mm



Normal	Miniature	L	ψD	Н	ψd
MFP-12	MFP25S	$3.4 \pm 0.3$	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
MFP204	-	$3.4 \pm 0.3$	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
MFP-25	MFP50S	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05
MFP207	-	$6.3 \pm 0.5$	$2.4 \pm 0.2$	28 ± 2.0	0.55 ± 0.05
MFP-50	MFP1WS	9.0 ± 0.5	$3.3 \pm 0.3$	26 ± 2.0	0.55 ± 0.05
MFP100	MFP2WS	11.5 ± 1.0	$4.5 \pm 0.5$	35 ± 2.0	0.8 ± 0.05
MFP200	MFP3WS	15.5 ± 1.0	5.0 ± 0.5	33 ± 2.0	0.8 ± 0.05

### **DERATING CURVE**





### **ELECTRICAL CHARACTERISTICS**

CHARACTERISTICS	MFP-12	MFP204	MFP-25	MFP207	MFP-50	MFP100	MFP200
Power Rating at 70 °C	1/6W	0.4W	1/4W	0.6W	1/2W	1W	1W
Maximum Working Voltage	150V	200V	250V	250V	350V	500V	500V
Maximum Overload Voltage	300V	400V	500V	600V	700V	1000V	1000V
Voltage Proof on Insulation	300V	300V	500V	500V	500V	1000V	1000V
Resistance Range	$10\Omega$ ~ 1MΩ for E192 series value						
Operating Temp. Range	- 55°C to +155°C						
Temperature Coefficient	±15ppm/°	C , ±25ppm/°	C, (±5ppm/°0	C, ±10ppm/°C	on request)		

CHARACTERISTICS	MFP25S	MFP50S	MFP1WS	MFP2WS	MFP3WS
Power Rating at 70 °C	1/4W	1/2W	1W	2W	3W
Maximum Working Voltage	200V	250V	400V	500V	500V
Maximum Overload Voltage	400V	600V	800V	1000V	1000V
Voltage Proof on Insulation	300V	500V	700V	1000V	1000V
Resistance Range	$10\Omega \sim 1M\Omega$ for E192 series value				
Operating Temp. Range	- 55°C to +155°C				
Temperature Coefficient	±15ppm/°C , ±25ppm/°C, (±5ppm/°C, ±10ppm/°C on request)				

Note: For resistance value out of above range is by request.

### **TEST AND REQUIRMENTS**

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)	± 0.25 % + 0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	Ву Туре
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5Kg(24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV(or Umax., whichever less) 10,000 cycles (1 Sec. on, 25 Sec.off)	±1.0%+0.05Ω



MFP

Damp Heat Steady State	IEC 60115-1 4.24	40±2°C,90-95% RH for 56 days, loaded with 0.1 times RCWV(or Umax., whichever less)	±1.5%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±1.5%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C → Room Temp. → +155°C → Room Temp.(5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.25%+0.05Ω

Note:.

### **RCWV (Rated Continuous Working Voltage):**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

 $V=\sqrt{(P X R)}$ 

or max. working voltage whichever is less

Where

V=Continuous rated DC or


AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value  $(\Omega)$ 



### **AXIAL / REEL TAPE SPECIFICATION**




Unit: mm

Normal	Miniature	a	Α	B1-B2 (Max.)	S (spacing)	T (max. deviation of spacing)
MED 40 MED050	6 ± 0.5	52.4 ± 1.5	1.2	<b>-</b> 5		
MFP-12	MFP25S	6 ± 0.5	26.0 ± 1.5	1	-5	
MFP204		6 ± 0.5	52.4 ± 1.5	1.2	<b>-</b> 5	_
WFP2U4	-	6 ± 0.5	26.0 ± 1.5	1	<del>-</del> 5	1 mm per 10 spacing, 0.5 mm per 5 spacing
MED OF	MEDEOC	0.05	52.4 ± 1.5	1.2	<del></del> 5	
MFP-25	MFP50S	$6 \pm 0.5$	26.0 ± 1.5	1		
MEDOOZ		0.05	52.4 ± 1.5	1.2	_	
MFP207	-	$6 \pm 0.5$	26.0 ± 1.5	1	<b>-</b> 5	
MFP-50	MFP1WS	6 ± 0.5	52.4 ± 1.5	1.2	5	
MED400		0.05	73.0 ± 1.5	1.5	-5	
MFP100	MFP2WS	$6 \pm 0.5$	52.4 ± 1.5	1.2		
MEDOOO	MEDOWC	0.05	73.0 ± 1.5	1.5		_
MFP200	MFP3WS	$6 \pm 0.5$	52.4 ± 1.5	1.2	<del>-</del> 10	




### **TAPE ON REEL PACKING**



TYPE Unit: mm/piece

Normal	Miniature	Across Flange(A)	В	Quantity Per Reel
MFP-12	MFP25S	66.5	75.5	5,000
MFP204	-	66.5	75.5	5,000
MFP-25	MFP50S	66.5	75.5	5,000
MFP207	-	66.5	75.5	5,000
MFP-50	MFP1WS	66.5	75.5	2,500
MFP100	MFP2WS	87	96	2,000
MFP200	MFP3WS	87	96	1,000

### **TAPE ON BOX PACKING**



TYPE		DIMENSIO		Unit: mm/piece	
Normal	Miniature	Α	В	С	Quantity Per Box
MFP-12	MFP25S	48	102	255	5,000
MFP-12	MFP25S	81	70	260	5,000
MFP204	-	48	102	255	5,000
MFP204	-	81	70	260	5,000
MFP-25	MFP50S	48	102	255	5,000
MFP-25	MFP50S	81	104	260	5,000
MFP-207	-	48	102	255	5,000
MFP-207	-	81	104	260	5,000
MFP-50	MFP1WS	73	45	258	1,000
MFP100	MFP2WS	81	78	260	1,000
MFP100	MFP2WS	103	91	260	1,000
MFP200	MFP3WS	81	91	260	1,000
MFP200	MFP3WS	103	94	260	1,000

### **BULK PACKING**

Normal	Miniature	Piece/Per Inner Box	Bag/Per Inner Box	Piece Per Bag
MFP-12	MFP25S	10,000	10	1,000
MFP204	-	10,000	10	1,000
MFP-25	MFP50S	10,000	10	1,000
MFP207	-	10,000	10	1,000
MFP-50	MFP1WS	5,000	5	1,000
MFP100	MFP2WS	2,000	4	500
MFP200	MFP3WS	1,000	2	500



### **MARKING**

COLOR	1st BAND	2nd BAND	3rd BAND	MULTIPLIER	TOLERANCE	
BLACK	0	0	0	1Ω		
BROWN	1	1	1	10Ω		
RED	2	2	2	100Ω		
ORANGE	3	3	3	1ΚΩ		
YELLOW	4	4	4	10ΚΩ		
GREEN	5	5	5	100K		
BLUE	6	6	6	1ΜΩ	± 0.25 % (C)	
VIOLET	7	7	7	10ΜΩ	± 0.1 % (B)	
GREY	8	8	8	0.001Ω	± 0.05 % (A)	
WHITE	9	9	9	0.0001Ω	± 0.02 % (P)	
GOLD				0.1Ω		
SILVER				0.01Ω		
±0.1 %, ±0.25%, ±0.05%, ±0.02%						
	_					
	5-BA	ND-CODE	_			



### **REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 3	Apr.2, 2024	-	<ul> <li>Added forming code description for part number and remove the forming type</li> </ul>
Version 2	Sep.6, 2023	-	<ul> <li>Updated legal disclaimer and footer versions numbers</li> </ul>
Version 1	Jul.13, 2022	-	- Added tolerance +/-0.02% color code
Version 0	Aug.2, 2021	-	- First issue of this specification

<sup>&</sup>quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."



#### **LEGAL DISCLAIMER**

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

