

## Product information

# 09 02 240 T

## Lineman's Pliers

With tether attachment point

American style

DIN ISO 5746 ASME B107.20



- High transmission ratio for easy cutting
- Requires 50 % less effort compared with conventional combination pliers thanks to optimised transmission ratio
- Pliers with tether attachment point for mounting a fall protection system
- Solid construction for heaviest strain; universally applicable
- Ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- Particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- Additional gripping zone below the joint for powerful leverage and pressing performance
- With cutting edges for soft and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Vanadium electric steel, forged, multi stage oil-hardened

### General

Article No.	09 02 240 T
EAN	4003773079941
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	460 g
Dimensions	240 x 56 x 23 mm
Standard	DIN ISO 5746 ASME B107.20
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm
Drop Protection System	yes

*technical change and errors excepted*



Gripping zone below the joint for powerful leverage

