


KVT-W90

Split cable glands



1

Description	Type	Order No. with locknut	Grommets small large	Thread Thread length	PU
-------------	------	---------------------------	---------------------------	-------------------------	----

Product description

The split KVT-W90 cable glands are used to insert and seal pre-terminated cables and conduits at a 90° angle.

In particular, the KVT 50-W90 is perfectly suited to hold corrugated or smooth hoses. A large number of cable entry grommets is available to the user.

Polyamide standard locknuts as well as a sealing ring are included in the shipment. Split locknuts can be ordered separately.

Advantages & benefits






- Installation at an angle of 90° to the cabinet
- Insertion of pre-terminated cables and conduits
- Warranty on pre-terminated cables remains
- Suitable for metric cut-outs

Specifications

Material	Polycarbonate (PC)
Colour	<input type="checkbox"/> grey (similar RAL 7035) <input checked="" type="checkbox"/> black
Flame class	UL94-V0, self-extinguishing
IP rating	IP54, with gasket and correct selection of the cable grommets (certified acc. to EN 60529)
Temperature Properties	- 30°C to + 100°C (static)
Cut-out dimension	Halogen-free, silicone-free Metric cut-outs

Accessories

Cable grommets	44 - 48
KVT-EMC Brackets	129
KGM Locknuts	170 - 171
ST Plugs	49

	KVT 32-W90	<input type="checkbox"/> 45404 <input checked="" type="checkbox"/> 45406	1 -	M32 x 1.5 Length: 11.5 mm	10
	GMT 32	<input checked="" type="checkbox"/> 31120	-	M32 x 1.5	10
	KVT 50 4-W90	<input type="checkbox"/> 45424 <input checked="" type="checkbox"/> 45426	4 -	M50 x 1.5 Length: 11.5 mm	5
	KVT 50 1-W90	<input type="checkbox"/> 45414 <input checked="" type="checkbox"/> 45416	- 1	M50 x 1.5 Length: 11.5 mm	5
	GMT 50	<input checked="" type="checkbox"/> 31140	-	M50 x 1.5	10

*Only valid for grey product types