

## Roller trolley

Yale

### Application:

Suitable for the insertion in all manual lifting devices.

### Execution:

- Calculated in line with DIN 15018
- Complies with BGV D6 cranes
- Can be adjusted for various profiles (INP, IPE, IPB and other beam ranges)
- Low design height
- Accurate positioning thanks to lug arm with counter-thread
- Central suspension, permanently lubricated runners, sealed and mounted on ball bearing
- Anti-tipping mechanism and wheel failure supports fitted as standard



<b>Art. no.</b>	<b>77167 110</b>
<b>Brand</b>	YALE
<b>Manufacturer Part Number</b>	05 14 1274
<b>Load-carrying capacity</b>	1000 kg
<b>Min. flange width</b>	50 mm
<b>Max. flange width</b>	220 mm
<b>Min. curve radius</b>	0.9 m
<b>Gross Weight</b>	9.600 kg
<b>Product Group</b>	7EE

### EAN

402509205488 1