


## Data sheet

### SM 031 (031-1CD30)

#### Technical data

|   |   |
|---|---|
| <b>Order no.</b>  | <b>031-1CD30</b>  |
| Type  | SM 031  |
| Module ID   | 040D 1544   |
| <b>General information</b>                              |   |
| Note  | -   |
| Features  | 4 inputs 16Bit<br>Voltage 0...10 V  |
| <b>Current consumption/power loss</b>                   |   |
| Current consumption from backplane bus                  | 60 mA   |
| Power loss  | 0.9 W   |
| <b>Technical data analog inputs</b>                     |   |
| Number of inputs  | 4   |
| Cable length, shielded                                  | 200 m   |
| Rated load voltage                                      | DC 24 V   |
| Current consumption from load voltage L+ (without load) | 25 mA   |
| Voltage inputs  |  |
| Min. input resistance (voltage range)                   | 200 kOhm  |
| Input voltage ranges                                    | 0 V ... +10 V   |
| Operational limit of voltage ranges                     | +/-0.2%   |
| Operational limit of voltage ranges with SFU            | -   |
| Basic error limit voltage ranges                        | +/-0.1%   |
| Basic error limit voltage ranges with SFU               | -   |
| Destruction limit current                               | -   |
| Current inputs  | -   |
| Max. input resistance (current range)                   | -   |
| Input current ranges                                    | -   |
| Operational limit of current ranges                     | -   |
| Operational limit of current ranges with SFU            | -   |
| Basic error limit current ranges                        | -   |
| Radical error limit current ranges with SFU             | -   |
| Destruction limit current inputs (voltage)              | -   |
| Destruction limit current inputs (electrical current)   | -   |
| Resistance inputs                                       | -   |
| Resistance ranges                                       | -   |
| Operational limit of resistor ranges                    | -   |
| Operational limit of resistor ranges with SFU           | -   |
| Basic error limit                                       | -   |
| Basic error limit with SFU                              | -   |
| Destruction limit resistance inputs                     | -   |
| Resistance thermometer inputs                           | -   |
| Resistance thermometer ranges                           | -   |

|   |                          |
|---|--------------------------|
| Operational limit of resistance thermometer ranges          | -                        |
| Operational limit of resistance thermometer ranges with SFU | -                        |
| Basic error limit thermoresistor ranges                     | -                        |
| Operational limit of resistance thermometer ranges with SFU | -                        |
| Destruction limit resistance thermometer inputs             | -                        |
| Thermocouple inputs   | -                        |
| Thermocouple ranges   | -                        |
| Operational limit of thermocouple ranges                    | -                        |
| Operational limit of thermocouple ranges with SFU           | -                        |
| Basic error limit thermoelement ranges                      | -                        |
| Basic error limit thermoelement ranges with SFU             | -                        |
| Destruction limit thermocouple inputs                       | -                        |
| Programmable temperature compensation                       | -                        |
| External temperature compensation                           | -                        |
| Internal temperature compensation                           | -                        |
| Internal temperature compensation                           | -                        |
| Technical unit of temperature measurement                   | -                        |
| Resolution in bit   | 16                       |
| Measurement principle                                       | successive approximation |
| Basic conversion time                                       | 480 µs all channels      |
| Noise suppression for frequency                             | >80dB at 50Hz (UCM<9V)   |

#### Status information, alarms, diagnostics

|                                  |                      |
|----------------------------------|----------------------|
| Status display                   | yes                  |
| Interrupts                       | yes, parameterizable |
| Process alarm                    | yes, parameterizable |
| Diagnostic interrupt             | yes, parameterizable |
| Diagnostic functions             | yes                  |
| Diagnostics information read-out | possible             |
| Module state                     | green LED            |
| Module error display             | red LED              |
| Channel error display            | red LED per channel  |

#### Isolation

|   |                  |
|---|------------------|
| Between channels  | -                |
| Between channels of groups to                               | -                |
| Between channels and backplane bus                          | ✓                |
| Between channels and power supply                           | ✓                |
| Max. potential difference between circuits                  | -                |
| Max. potential difference between inputs (Ucm)              | DC 9 V           |
| Max. potential difference between Mana and Mintern (Uiso)   | -                |
| Max. potential difference between inputs and Mana (Ucm)     | -                |
| Max. potential difference between inputs and Mintern (Uiso) | DC 75 V/ AC 60 V |
| Max. potential difference between Mintern and outputs       | -                |
| Insulation tested with                                      | DC 500 V         |

#### Datasizes

|              |   |
|--------------|---|
| Input bytes  | 8 |
| Output bytes | 0 |

|                  |    |
|------------------|----|
| Parameter bytes  | 32 |
| Diagnostic bytes | 20 |

### Housing

|          |                    |
|----------|--------------------|
| Material | PPE / PPE GF10     |
| Mounting | Profile rail 35 mm |

### Mechanical data

|                    |                            |
|--------------------|----------------------------|
| Dimensions (WxHxD) | 12.9 mm x 109 mm x 76.5 mm |
| Weight             | 60 g                       |

### Environmental conditions

|                       |                 |
|-----------------------|-----------------|
| Operating temperature | 0 °C to 60 °C   |
| Storage temperature   | -25 °C to 70 °C |

### Certifications

|                     |     |
|---------------------|-----|
| UL508 certification | yes |
|---------------------|-----|