15021Z 2000W 235V UNP

Product family description

Tubular double-ended infrared halogen lamp used as highpower and high-efficiency heat source for zone-heating and various industrial application with a specific HeLeN coating reducing glare emission

Product Features

,___

- Lower visible glare compared to clear or Ruby lamps, thanks to the unique HeLeN coating
- Improved colour rendering

Product Benefits

- Instant heat: full power within 1 second at switching on
- Glare reduction: the visible glare is strongly reduced thanks to the Philips unique HeLeN coating
- Improved colour rendering compared to Ruby / Red tube lamps
- Clean: no by product and no pollution emitted by Infrared lamps
- Safe: heat shock resistant lamp thanks to its quartz envelop
- Economical: more than 85% of the consumed energy is transmitted into infrared heat
- Fully dimmable: Infrared lamps are accurately controllable (0% to 100%)
- Possibility to put sensor: On/Off switches do not affect life time of Infrared lamps
- Heat can be focused: Infrared lamps have the same optical properties as light, meaning that the heat can be directed by reflectors
- Compact heat source: Infrared lamps have a narrow diameter

Application

• Zone heating in patios, Restaurant and café terraces, factories, sports halls, exhibition halls, work areas, churches, large halls, warehouses, storage areas,



garages, greenhouses, open air applications, stadiums, camp sites, de-icing

• Process heating where glare reduction is needed, such as paint drying

Product data						
Order code	519061 25					
Full product name	15021Z 2000W 235V UNP					
Packing type	Unpacked					
Pieces per pack						
Net weight per piece	0.048 KG					
Successor order code						
Philips Code	15021Z					
Cap-Base	SK15					
Cap-Base Information	Fasten					
Bulb	тн					
Bulb Finish	HELEN Sleeve					
Execution	Straight					
Operating Position	any					
Main Application	Cooking					
Packing Type	UNP [Unpacked]					
Packing Configuration	10					
Life to 50% failures	5000 hr					
Lamp Wattage	2000W					
Voltage	235V					




XHIRSTRC











Cap-Base SK15

Operating Position any







Preferably do not touch quartz with bare hands. If grease or chemical compound have been deposited on quartz, simply clean before lighting with cloth moistened with alcohol.

Permissible temperature





Disconnect installation from power supply before removing or installing a lamp.



Prolonged looking at the lamp during operation may result in damage on the eye.




Keep dry.



Non-household





XHIRSTRC

	А	А	А	А	А	А
Full produc t name	Min	Min	Nom	Nom	Max	Max
15021 Z 2000 W 235V UNP	306	306	-	-	-	-

	С	С	С	С	С	С
Full produc t name	Min	Min	Nom	Nom	Max	Max
15021 Z 2000 W 235V UNP	-	-	-	-	355	355

	D	D	W	W	Х	Х
Full produc t name	Max	Max	Nom	Nom	Nom	Nom
15021 Z 2000 W	П	П	280	280	300	300



	D	D	W	W	Х	Х	
Full produc t name 235V UNP	Max	Max	Nom	Nom	Nom	Nom	
Full product name							
15021Z 2000W 235V UNP							



©2009 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liablity will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights. Document order number : 0000 000 00000