

T255M0HIRX2



Article Number: 111-25300

Heavy Duty Cable Tie, 22" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg



Download spec sheet

Base Data

Local Order Number	T255M0HIRX2
Type	T255M
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • High impact, heat and UV stabilized heavy duty cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 22" Long, 250 lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	250.0 lbs
Minimum Tensile Strength (Metric)	1115.0 N
Length L (Imperial)	22.0 "
Length L (Metric)	560.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.5 "
Width W (Metric)	12.6 mm
Bundle Diameter Min. (Imperial)	0.49 "
Bundle Diameter Min. (Metric)	12.5 mm
Bundle Diameter Max. (Imperial)	6.3 "
Bundle Diameter Max. (Metric)	160.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	25
Carton Quantity	500

Material and Specifications

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut PA66HIRHSUV
Flammability UL94 HB
Operating Temperature -40°F to +230°F (-40°C to +110°C)
ROHS Compliant Yes
Certification/Specification UL-ZODZ2.E64139
UL Listed (US and Canada) No
UL Recognized (US and Canada) No
