

## Data sheet

### CP 040 RS422/485 (040-1CA00)

#### Technical data

<b>Order no.</b>	<b>040-1CA00</b>
Type	CP 040 RS422/485
Module ID	0E41 1700
<b>General information</b>	
Note	-
Features	RS422/485 interface
<b>Current consumption/power loss</b>	
Current consumption from backplane bus	100 mA
Current consumption from load voltage L+ (without load)	10 mA
Power loss	1 W
<b>Status information, alarms, diagnostics</b>	
Status display	yes
Interrupts	yes, parameterizable
Process alarm	no
Diagnostic interrupt	yes, parameterizable
Diagnostic functions	yes, parameterizable
Diagnostics information read-out	possible
Supply voltage display	green LED
Group error display	red LED
Channel error display	red LED
<b>Point-to-point communication</b>	
PtP communication	✓
Interface isolated	✓
RS232 interface	-
RS422 interface	✓
RS485 interface	✓
Connector	Terminal module
Transmission speed, min.	150 bit/s
Transmission speed, max.	115.2 kbit/s
Cable length, max.	1200 m
<b>Point-to-point protocol</b>	
ASCII protocol	✓
STX/ETX protocol	✓
3964(R) protocol	✓
RK512 protocol	-
USS master protocol	-
Modbus master protocol	✓

Modbus slave protocol



Special protocols

-

### Datasizes

Input bytes 8 / 20 / 60

Output bytes 8 / 20 / 60

Parameter bytes 23

Diagnostic bytes 20

### Housing

Material PPE / PPE GF10

Mounting Profile rail 35 mm

### Mechanical data

Dimensions (WxHxD) 12.9 mm x 109 mm x 76.5 mm

Weight 60 g

### Environmental conditions

Operating temperature 0 °C to 60 °C

Storage temperature -25 °C to 70 °C

### Certifications

UL508 certification yes