

DWLN insert holder, negative left

For contour and longitudinal turning with WN indexable insert



Application:

For contour and longitudinal turning with WN indexable insert, 80°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type W, pitch angle 95°, tip angle 80°, clearance angle 0°

Advantage:

- Optimum repeat and positioning accuracy
- Minimised vibration and extended service life
- The insert setting is protected by a cemented carbide backing
- Extremely robust clamping system

Art. no.	17684 116
Brand	WIDIA
Manufacturer Part Number	5696754
ISO name	DWLN R/L 2525 M08
Knife edge length	8 mm
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Programming size	32 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Left
Length of head	25 mm
Gross Weight	0.761 kg
Product Group	1XG

EAN

4050841489126