

Horizontal quick-action clamp

With open clamping arm and horizontal base



Application:


For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

Delivery:

With thrust bolt and protective cap



Art. no.	26215 010
Size	1
Min./max. hole distance	13-14.5 mm
Min./max. distance between stop and centre of drill	18-21.5 mm
Bore diameter	5.2 mm
Clamping height	19 mm
Retaining force	800 N
Max. tensile force	1100 N
Height	30 mm
Length 2	120 mm
Thumbscrew size	M5 x 30 mm

EAN-Code

4020772093013