Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: SPL	

Supplier's address: Schiefer Lighting, Potterbakkerstraat 35, 4871EP Etten-Leur, NL

Model identifier: LX0)23961305
-----------------------	-----------

Type of light source:	Type	of light	source:
-----------------------	------	----------	---------

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type	E27		
(or other electric interface)			
Mains or non-mains:	MLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes

Product parameters

Product parameters				
Parameter		Value	Parameter	Value
General product parameters:				
Energy consur mode (kWh/10 up to the neare	00 h), rounded	4	Energy efficiency class	G
dicating if it refe a sphere (360°)	s flux (фuse), in- ers to the flux in , in a wide cone arrow cone (90º)	200 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 000
On-mode pow pressed in W	ver (P _{on}), ex-	4,0	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00
(P _{net}) for CLS, 6	candby power expressed in W the second dec-	-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	90
Outer dimen-	Height	140	Spectral power dis-	See image
sions without	Width	64	tribution in the	in last page
separate con- trol gear, light- ing control	Depth	64	range 250 nm to 800 nm, at full-load	

parts and non- lighting con- trol parts, if any (millime-			
tre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordi-	0,527
		nates (x and y)	0,416
Parameters for LED and OLED lig	ght sources:		
R9 colour rendering index value	62	Survival factor	0,90
the lumen maintenance factor	0,96		
Parameters for LED and OLED mains light sources:			
displacement factor (cos φ1)	0,85	Colour consistency in McAdam ellipses	6
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	_(b)	If yes then replace- ment claim (W)	-
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,3

(a)'-': not applicable; (b)'-': not applicable;

