

Electronic micrometer

ABS Digimatic QuickMike

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- IP65
- ABS function
- ON/OFF
- Non-rotating spindle
- HOLD (measured value storage)
- Origin (measurement presetting)

Advantage:

- Faster movement
- IP65

Delivery:

Includes box, set standard (25 mm or more), battery



Art. no.	32017 643
Brand	MITUTOYO
Manufacturer Part Number	293-669-20
Display	Digital
Min./max. length measuring range	75-105 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	No
Digit height	10 mm
Functions	ABS function, Hold-function (AE lock), On/Off, Preset function, Origin (Dimension preset), Absolute function
Min./max. measurement force	5-12 N
Error limit	3 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	60 mm
Measuring spindle increments	10 mm
Calibration Group	D
Gross Weight	1.190 kg
Product Group	3MA

EAN

4946368736723