

Flat-bed hand truck, 2-axle

With board walls, carrying capacity 700 to 1250 kg

fetra
Transportgeräte

Execution:

- Module system
- From welded profiled steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Loading area covered with slip-resistant phenolic resin coated waterproof plywood
- Side plates 250/325 mm high, 3 hinged sides, front wall fixed
- Side walls made of steel pipe frame, powder-coated, with fillings from water-resistant plywood
- Wheels either with solid rubber or air tyres, hubs with roller bearings
- Automatic parking brake acting on the front wheels, according to EN 1757-3
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



Art. no.	50267 848
Brand	FETRA
Manufacturer Part Number	6456L
Design	With walls
Material of loading surface	Wood
Length	2360 mm
Height	1200 mm
Loading surface length	2000 mm
Width	1025 mm
Loading-surface width	1000 mm
Loading surface size	2000 x 1000 mm
Load-carrying capacity	1250 kg
Colour	Brilliant blue RAL 5007
With wheel lock	Yes
Total stop optional	No
Wheel width	100 mm
Wheel diameter	400 mm
Material of wheel	Air
Surface	Powder-coated
Gross Weight	137.000 kg
Product Group	5AE

EAN

4017976014142