

Hinged-door cabinets

With rack for tool holder no. 50655 020-130

Application:

For secure and clearly-laid-out storage and retrieval of CNC tools

Version:

- Housing in robust steel sheet with hinged doors, cylinder lock with 2 keys
- In the cabinet, there is a built in storage and retrieval rack with 7 supporting profiles for one-sided storage
- Four tool holders can be placed on each supporting profile
- Storage capacity: 28 tool holders
- integrated fork lift-compatible base with removable screen for in-house transport
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020

Delivery:

without tool carrier



Art. no.	50656 305
Door design	Full-sheet panel
Number of tool carriers	28 PCS
Height	1950 mm
Width	1015 mm
Depth	620 mm
Number of carrier sections	7 PCS
Load-carrying capacity per carrier section	50 kg
Load-carrying capacity	700 kg
Central locking	Yes
Lock type	DOM® locking system
Material	Sheet steel
Body colour	Optional
Colour of front	Optional
Surface	Powder-coated

EAN-Code

4039247520329