



EMBEDDED INDUSTRIAL  
DEVELOPMENT PLATFORM



# DIGI CONNECTCORE 8M MINI DEVELOPMENT KIT

Complete development platform for embedded industrial product designs

The Digi ConnectCore® 8M Mini development kit is a cohesive and cost-effective System-on-Module (SOM) platform built on the NXP® i.MX 8M Mini applications processor. It integrates memory, Digi Microcontroller Assist™ power management, a pre-certified wireless connectivity and advanced Digi TrustFence® device security with a complete, open-source Linux software platform based on the Yocto Project and complete Android support through Digi Embedded Android.

The SOM platform simplifies embedded product development by eliminating the complexity and risk of custom board designs. The Digi ConnectCore 8M Mini development kit provides multiple display interfaces, camera, audio, Digi XBee® modules and other hardware options for optimal flexibility and user experience.

Digi ConnectCore 8M Mini strikes an optimal balance of performance, power and cost. It's suitable for a wide range of industrial, medical, transportation and agricultural products, and features scalable, power-efficient ARM® Cortex®-A53 and Cortex-M4 processors, rich multimedia and advanced connectivity. Digi ConnectCore 8M Mini is ideal for Internet of Things (IoT) applications such as Human Machine Interface (HMI), equipment monitoring, audio/voice, edge compute and machine learning. The development board includes two Digi XBee connectors to enable cellular, short- and long-range connectivity.

With twenty years of embedded SOM experience enabling millions of globally connected products, Digi is a trusted embedded and IoT solutions provider, simplifying the way customers design, build and deploy connected applications. Digi also offers cellular integration support, certification assistance, and custom design and build services to get your products to market smarter and faster.

## THE KIT INCLUDES:

- ✓ Digi ConnectCore® 8M Mini development board
- ✓ Console port cable
- ✓ Dual-band antenna
- ✓ Power supply and accessories
- ✓ Reference designs for LVDS, HDMI and CAN-FD

PART NUMBER	DESCRIPTION
CC-WMX8MM-KIT	Digi ConnectCore 8M Mini development kit

## FEATURES AND BENEFITS

- Industrial i.MX 8M Mini quad-core System-on-Module (SOM)
- Digi Embedded Yocto (Linux) providing full Yocto Project support
- Digi Embedded Android providing full Android support
- Video capabilities with built-in VPU
- Digi TrustFence, a complete IoT device security framework
- Digi Microcontroller Assist™ for advanced power management, security, peripheral support and system reliability operations
- Pre-certified dual-band 802.11a/b/g/n/ac and Bluetooth® 5 connectivity
- Cloud and edge compute services integration
- Dev board includes on-board interfaces for:
  - HDMI or LVDS displays
  - Digi XBee integration to extend wireless connectivity to a global family of modules spanning popular IoT protocols

## SPECIFICATIONS

## Digi ConnectCore® 8M Mini Development Board

## PERFORMANCE

## APPLICATION PROCESSOR

- NXP® i.MX 8M Mini Quad GPU Industrial
- Four Cortex®-A53 cores up to 1.6 GHz
  - Cortex-M4 400 MHz core processor for low-power processing

## MEMORY

Up to 8 GB eMMC, up to 2 GB LPDDR4 (32-bit)

## WIRED NETWORK CONNECTIVITY

## ETHERNET

Gigabit Ethernet 10/100/1000 with RJ-45 connector

## WIRELESS NETWORK CONNECTIVITY

## WI-FI

802.11a/b/g/n/ac 1x1 (MCS 0-9) with strong WPA2-enterprise authentication/encryption for Wi-Fi connections

## BLUETOOTH®

Bluetooth 5 with Bluetooth Low Energy support

## ANTENNAS

SMA antenna connector

## DIGI XBEE® RF

Two Digi XBee sockets, one supporting Digi XBee Cellular

## PERIPHERALS/INTERFACES

## USB

Two USB host (dual Type A)

## GPIO

Five GPIOs

## UART / CONSOLE

USB console

## OTHER CONNECTIVITY

CAN-FD; RS-485

## PCI EXPRESS MINI CARD

Full-size card support with USB connection and on-board micro-SIM slot support

## EXTERNAL STORAGE

MicroSD connector

## AUDIO

3.5 mm headphone jack; 3.5 mm microphone jack; two speaker output; line-out output; two line-in input

## BUTTONS / SWITCHES

Reset button; on/off button (supporting power-on/off and suspend/resume functionality); two user buttons

## DEBUG

SW for MCA (Tag-connect); JTAG for i.MX 8M Nano CPU; USB for System-on-Module recovery

## LEDS

Three user LEDs

## MULTIMEDIA

## DISPLAY

HDMI; LVDS with backlight control and I2C touch interface; MIPI-DSI; note: only one display interface can work at a time

## CAMERA

MIPI-CSI camera connector supporting two data lanes (two additional data lanes available in expansion connector)

## POWER REQUIREMENTS

## SUPPLY VOLTAGE

5 VDC

## POWER CONNECTORS

5 V input power jack connector; supercap populated in development board supporting RTC applications; coin-cell/supercap connector; battery connector

## ENVIRONMENTAL

## OPERATING TEMPERATURE

-40° C to 85° C (-40° F to 185° F)

## STORAGE TEMPERATURE

-50° C to 125° C (-58° F to 257° F)

## RELATIVE HUMIDITY

5% to 90% (non-condensing)

## MECHANICAL DIMENSIONS

130 mm x 210 mm (5.12 in x 8.27 in)

**DIGI SERVICE AND SUPPORT** / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit [www.digi.com/support](http://www.digi.com/support).

© 1996-2021 Digi International Inc. All rights reserved.  
All trademarks are the property of their respective owners.

91004459  
A3/321

**DIGI INTERNATIONAL WORLDWIDE HQ**  
877-912-3444 / 952-912-3444 / [www.digi.com](http://www.digi.com)

**DIGI INTERNATIONAL JAPAN**  
+81-3-5428-0261 / [www.digi-intl.co.jp](http://www.digi-intl.co.jp)

**DIGI INTERNATIONAL GERMANY**  
+49-89-540-428-0

**DIGI INTERNATIONAL SINGAPORE**  
+65-6213-5380

**DIGI INTERNATIONAL CHINA**  
+86-21-50492199 / [www.digi.com.cn](http://www.digi.com.cn)

